




NOTES:
1. ALL PARTS TO BE BULK PACKED.
2. ALL DIMENSIONS ARE REFERENCE EXCEPT THOSE WITH A TOLERANCE.




FACE VIEW
8382-2PG-3XX




FACE VIEW
8382-3PG-3XX



FACE VIEW
8382-4PG-3XX



FACE VIEW
8382-5PG-3XX



WIRE VIEW
8382-5PG-3XX


ASS'Y P/N	GROMMET SIZE
8382-XPG-3DC	DAISY CHAIN
8382-XPG-311	CABLE O.D. .09-.14 [2.3-3.6]
8382-XPG-315	CABLE O.D. .15-.17 [3.8-4.3]
8382-XPG-318	CABLE O.D. .18-.20 [4.6-5.1]
8382-XPG-321	CABLE O.D. .21-.23 [5.3-5.8]

KIT P/N	NO. OF CONTACTS
8382-2PG-3XX	2
8283-3PG-3XX	3
8283-4PG-3XX	4
8283-5PG-3XX	5
8283-XPG-3XX	


GROMMET SIZE
FOR SINGLE
GROMMET OR "DC"
FOR DAISY CHAIN

NO. OF CONTACTS


DAISY CHAIN GROMMET
FOR 8382-XPG-3DC
MAT'L: RUBBER, BLACK




CABLE CONNECTOR, MALE
MAT'L: NYLON, BLACK



(2-5) PIN CONTACTS
SOLDER TYPE
MAT'L: GOLD PLATED
COPPER ALLOY



SINGLE GROMMET
8382-XPG-311 .125 I.D. FOR CABLE .09-.14 O.D. [2.3-3.6]
8382-XPG-315 .188 I.D. FOR CABLE .15-.17 O.D. [3.8-4.3]
8382-XPG-318 .156 I.D. FOR CABLE .18-.20 O.D. [4.6-5.1]
8382-XPG-321 .225 I.D. FOR CABLE .21-.23 O.D. [5.3-5.8]



BACKSHELL
MAT'L: NYLON, BLACK

DIMENSIONS IN BRACKETS [] ARE METRIC

RoHS COMPLIANT

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT / INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A	MA	02-12-18	DRAWING CREATED PER DOR 15-E253SL #20		
REV.	INIT.	DATE	DESCRIPTION		
	MA	02-12-18	ORIG. DRAWN BY: DATE: MA 02-12-18	 601 E. WILDWOOD VILLA PARK, IL 60181	
			CHECKED BY:		
			APPROVED BY:	TITLE: CONNECTOR ASSEMBLY (2-5) #16 PIN CONTACTS MINI-CON-X	
			SCALE: NTS	SIZE: B	SHEET: 1 OF 1
			FILE: 8382-XPG-3XX	DIRECTORY: SLW	PART NUMBER: 8382-XPG-3XX
					REV A