

# FC to ST 9/125 Adapter for Multi-Function Optical Fiber Cable Tester (M/F)

MODEL NUMBER: **T020-001-ST9**



Converts FC connector on Tripp Lite Multi-Function Optical Fiber Cable Tester to an ST connector. Ideal for cable installers or anyone else working in telecom or LAN environments.

## Description

The T020-001-ST9 FC to ST 9/125 Adapter converts a native FC fiber female port on the T020-001-PSF Multi-Function Optical Fiber Cable Tester to an ST female port for 9/125 singlemode cable testing. "9/125" is clearly labeled on the unit to differentiate the T020-001-ST9 from other adapters. Included dust caps keep the connectors clean when not in use.

## Features

### Converts Cable Tester's FC Connector to an ST Connector

- Ideal for cable installers or anyone else working in telecom or LAN environments
- Perfect for 9/125 singlemode cable testing
- FC male plug connects to cable tester's FC female jack
- Included dust caps keep connectors clean
- For use with T020-001-PSF Multi-Function Optical Fiber Cable Tester

## Specifications

OVERVIEW	
UPC Code	037332197672
Technology	Singlemode
PHYSICAL	
Color	Silver
Clad Diameter (microns)	125
Core Diameter (microns)	9

## Highlights

- Converts native FC jack to an ST female connector
- FC male plug connects to fiber cable tester's FC female jack
- Perfect for 9/125 singlemode cable testing
- Included dust caps keep connectors clean
- For use with T020-001-PSF Optical Fiber Cable Tester

## System Requirements

- T020-001-PSF Multi-Function Optical Fiber Cable Tester

## Package Includes

- T020-001-ST9 FC to ST 9/125 Adapter



Powering Business Worldwide



Shipping Dimensions (hwd / in.)	9.00 x 7.00 x 0.50
Shipping Dimensions (hwd / cm)	22.86 x 17.78 x 1.27
Shipping Weight (lbs.)	0.04
Shipping Weight (kg)	0.02
<b>STANDARDS &amp; COMPLIANCE</b>	
Product Compliance	RoHS
<b>WARRANTY &amp; SUPPORT</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard  
Cleveland, OH 44122  
United States  
<https://tripplite.eaton.com>

© 2024 Eaton. All Rights Reserved.  
Eaton is a registered trademark. All other trademarks  
are the property of their respective owners.