





1 MATERIAL: HOUSING: NYLON, UL94V-0, RED
CONTACTS: BRASS, TIN-PLATED



24	46.2±0.25 [1.82±.01]	51.6 [2.03]	55.6 [2.19]	2-2029138-4
22	42.0±0.25 [1.65±.01]	47.4 [1.87]	51.4 [2.02]	2-2029138-2
20	37.8±0.25 [1.49±.01]	43.2 [1.70]	47.2 [1.86]	2-2029138-0
18	33.6±0.25 [1.32±.01]	39.0 [1.54]	43.0 [1.69]	1-2029138-8
16	29.4±0.25 [1.16±.01]	34.8 [1.37]	38.8 [1.53]	1-2029138-6
14	25.2±0.25 [.99±.01]	30.6 [1.21]	34.6 [1.36]	1-2029138-4
12	21.0±0.25 [.83±.01]	26.4 [1.04]	30.4 [1.20]	1-2029138-2
10	16.8±0.13 [.66±.005]	22.2 [.87]	26.2 [1.03]	1-2029138-0
8	12.6±0.13 [.50±.005]	18.0 [.71]	22.0 [.87]	2029138-8
6	8.4±0.13 [.33±.005]	13.8 [.54]	17.8 [.70]	2029138-6
4	4.2±0.13 [.17±.005]	9.6 [.38]	13.6 [.54]	2029138-4
2	-	5.4 [.21]	9.4 [.37]	2029138-2
POS	A	B±0.25 [.01]	C±0.38 [.015]	PART NUMBER



PCB LAYOUT: COMPONENT SIDE
RECOMMENDED BOARD THICKNESS 1.78 [.070]



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	±	
1 PLC	±	0.13 [.005]
2 PLC	±	0.25 [.010]
3 PLC	±	-
4 PLC	±	-
ANGLES	±	
FINISH		

MATERIAL

1

DWN
K. WHITAKER

CHK
C. CASH

APVD
C. CASH

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

13AUG2008

13AUG2008

13AUG2008

NAME

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-2029138

RESTRICTED TO
-

SCALE
10:1

SHEET
1 OF 1

REV
A

Tyco
Electronics

Tyco Electronics Corporation
Harrisburg, PA 17105-3608

VERTICAL HEADER, RED,
WITH PEGS, WITH DRAIN HOLES,
VAL-U-LOK(TM)