





TABLE 1

| DASH No.      | Dim. | Amount of Pins | Dim.A | Dim.B | Dim.C |
|---------------|------|----------------|-------|-------|-------|
| -000 06 XX LF | 6    |                | 2.54  | 18.31 | 8.46  |
| -000 10 XX LF | 10   |                | 5.08  | 20.85 | 11.00 |
| -000 12 XX LF | 12   |                | 6.35  | 22.12 | 12.27 |
| -000 14 XX LF | 14   |                | 7.62  | 23.39 | 13.54 |
| -000 16 XX LF | 16   |                | 8.89  | 24.66 | 14.81 |
| -000 20 XX LF | 20   |                | 11.43 | 27.20 | 17.35 |
| -000 26 XX LF | 26   |                | 15.24 | 31.01 | 21.16 |
| -000 30 XX LF | 30   |                | 17.78 | 33.55 | 23.70 |
| -000 34 XX LF | 34   |                | 20.32 | 36.09 | 26.24 |
| -000 40 XX LF | 40   |                | 24.13 | 39.90 | 30.05 |
| -000 44 XX LF | 44   |                | 26.67 | 42.44 | 32.59 |
| -000 50 XX LF | 50   |                | 30.48 | 46.25 | 36.40 |
| -000 60 XX LF | 60   |                | 36.83 | 52.60 | 42.75 |
| -000 64 XX LF | 64   |                | 39.37 | 55.14 | 45.29 |
| -000 66 XX LF | 66   |                | 40.64 | 56.41 | 46.56 |
| -000 68 XX LF | 68   |                | 41.91 | 57.68 | 47.83 |



## NOTE:

- MATERIAL:  
HOUSING: HIGH TEMP PLASTIC, UL94-V0, BLACK  
TERMINAL: COPPER ALLOY, SQ=0.40±0.03MM
- FINISH:  
TERMINAL: GOLD AT CONTACT,  
G/F OVER 1um(40u") MIN Ni OVER ALL
- SPEC.:  
PRODUCT SPEC: GS-12-629  
PACKING SPEC: GS-14-1420
- THE HSG. WILL WITHSTAND EXPOSURE TO 260C  
PEAK TEMP. FOR 10 SEC. IN A CONVECTION INFRA-RED  
OR VAPOR PHASE REFLOW OVEN.
- PRODUCT NUMBERING:  
20021621 - 0 0 0 XX X X LF

LEAD FREE

PLATING:

1:GOLD FLASH ALL OVER  
4:0.25um(10U")GOLD AT CONTACT  
8:0.76um(30U")GOLD AT CONTACT  
9:1u" GOLD OVER 30u" PdNi AT CONTACT

PACKING

T: TUBE  
D: TUBE + CAP  
C: T&R + CAP (30 POS)

PIN COUNT

SEE TABLE 1

|             |  |                |  |                    |  |                             |  |                                                                                                     |  |                           |  |                                     |  |                                                                                              |  |          |  |                          |  |      |  |
|-------------|--|----------------|--|--------------------|--|-----------------------------|--|-----------------------------------------------------------------------------------------------------|--|---------------------------|--|-------------------------------------|--|----------------------------------------------------------------------------------------------|--|----------|--|--------------------------|--|------|--|
| mat'l. code |  |                |  | surface<br>ISO1302 |  | tolerance<br>ISO1101 ISO406 |  | projection<br> |  | product family<br>MINITEK |  |                                     |  |                                                                                              |  |          |  |                          |  |      |  |
| ltr         |  | ecn no         |  | dr                 |  | date                        |  | tolerances unless otherwise specified                                                               |  | title                     |  |                                     |  |                                                                                              |  |          |  |                          |  |      |  |
| A           |  | T09-1117       |  | S.LIN              |  | 09/15/09                    |  | angles                                                                                              |  | 0.X±0.38                  |  | 1.27X1.27MM BTB EJECT HEADER<br>SMT |  |                                                                                              |  |          |  |                          |  |      |  |
| B           |  | T10-0027       |  | S.LIN              |  | 01/20/10                    |  | 0°±2°                                                                                               |  | 0.XX±0.25                 |  |                                     |  |                                                                                              |  |          |  |                          |  |      |  |
| C           |  | T-005600       |  | S.LIN              |  | 01/16/12                    |  | 0°±2°                                                                                               |  | 0.XXX±0.10                |  |                                     |  |                                                                                              |  |          |  |                          |  |      |  |
| D           |  | EX-N-010367    |  | ZK                 |  | 01/16/12                    |  | dr                                                                                                  |  | STERLING LIN              |  | 09/15/09                            |  | FCI<br> |  | dwg no   |  | sheet 1 of 1             |  | size |  |
| E           |  | EX-N-010623    |  | ZK                 |  | 02/12/12                    |  | engr                                                                                                |  | STERLING LIN              |  | 09/15/09                            |  |                                                                                              |  | 20021621 |  | A4                       |  |      |  |
| F           |  | EX-N-1727      |  | TIM                |  | 03/20/14                    |  | chr                                                                                                 |  | GRAY HSIEH                |  | 09/15/09                            |  |                                                                                              |  |          |  |                          |  |      |  |
|             |  |                |  |                    |  |                             |  | appd                                                                                                |  | JOSEPH                    |  | 09/15/09                            |  |                                                                                              |  | type     |  | Product Customer Drawing |  |      |  |
| sheet index |  | revision sheet |  | F                  |  | 1                           |  |                                                                                                     |  |                           |  |                                     |  |                                                                                              |  |          |  |                          |  |      |  |