



1. FIGURE AND DIMENSIONS (视图及尺寸)



开孔尺寸



针芯性能参数表				
孔位排列	P02	P03	P04	P05
耐压 (V)	850	850	850	850
接触件直径 (mm)	φ1.0*2	φ1.0*3	φ0.7*4	φ0.7*5
工作电压 (V)	160V	160V	110V	110V
额定电流 (A)	4.5A	4.5A	2.7A	2.7A

Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	1000
2. Working Temperature (温度)	-40~+85°
3. IP Rating (防护级别)	IP 67
4. Diameter of socket end (插座端直径)	See the needle core parameter table/见针芯参数表
5. Rated voltage (额定电压)	
6. Rated Current (额定电流)	
7. Shell material (壳体材质)	
8. Pin Material (插针材料)	铜镀金 (Brass with gold plating)
9. Coupling (接插方式)	推入式快速锁紧 (Push-pull)
10. Insulator material (绝缘体材料)	PPS 耐高温230℃
11. Termination (接线方式)	焊接 (Solder)

Sum up (总结)	
Series (系列)	SF6
Shell style/model (外壳样式/型号)	-
Button (按键)	-
Termination type (终止类型)	-
Line diameter awg (线材直径)	-
Cable diameter φ (电缆直径)	-
Match plug (匹配插头)	

版本				TITLE	DRAWING NO.	REV.
REVA4					SF10. C12L03	A0
REVA3						
REVA2						
REVA1						
DRAW		DATE		PART NO.	UNIT	mm
CHECK		DATE			SCALE	Free
APPR'D		DATE			SHEET	IOF N
				USE	XKB INDUSTRIAL PRECISION CO., LIMITED	