


1. FIGURE AND DIMENSIONS (视图及尺寸)



针芯性能参数表				
孔位排列	P02	P03	P04	P05
耐压 (V)	450	450	450	450
接触件直径 (mm)	$\phi 0.6*2$	$\phi 0.6*3$	$\phi 0.6*4$	$\phi 0.6*5$
工作电压 (V)	27V	27V	27V	27V
额定电流 (A)	2.7A	2.7A	2.7A	2.7A

Main technical indicators (主要技术指标)	
1. Mating (插拔次数)	500
2. Working Temperature (温度)	-40~+85°
3. IP Rating (防护级别)	IP 44
4. Diameter of socket end (插座端直径)	See the needle core parameter table/见针芯参数表
5. Rated voltage (额定电压)	
6. Rated Current (额定电流)	
7. Shell material (壳体材质)	铜镀铬 (Brass with chrome plating)
8. Pin Material (插针材料)	铜镀金 (Brass with gold plating)
9. Coupling (接插方式)	推入式快速锁紧 (Push-pull)
10. Insulator material (绝缘体材料)	PPS 耐高温230℃
11. Termination (接线方式)	焊接 (Solder)

Sum up (总结)	
Series (系列)	SF6
Shell style/model (外壳样式/型号)	-
Button (按键)	-
Termination type (终止类型)	-
Line diameter awg (线材直径)	-
Cable diameter ϕ (电缆直径)	-
Match plug (匹配插头)	

版本				TITLE	DRAWING NO.	REV.
REVA4				PART NO.	SF6. C12L05	A0
REVA3						
REVA2						
REVA1						
DRAW		DATE				
CHECK		DATE		USE		
APPR'D		DATE				
KKB INDUSTRIAL PRECISION CO., LIMITED						