









1. MATERIAL: HOUSING: GLASS FILLED THERMO PLASTIC
POLYESTER(94V-0), COLOR: BLACK
CONTACT: COPPER ALLOY
RETENTION LEG: PRE-TIN COPPER ALLOY

2. FINISH(ALL OVER): NICKEL PL. 1.27μmMIN
3. FINISH(CONTACT OVER): TIN PL. 1.0μmMIN AFTER 2
4. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
	-		A	INITIAL	05DEC2018	F.Z



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1










AS SHOWN : I-2348454-0 (20POS:X-KEY)
ONLY 4POS---SEE SHEET 2 OF 3

20	X	9	22.5	26.0	27.6	I-2348454-0
16	X	7	17.5	21.0	22.6	I-2348454-8
12	X	5	12.5	16.0	17.6	I-2348454-6
10	X	4	10.0	13.5	15.1	I-2348454-5
8	X	3	7.5	11.0	12.6	I-2348454-4
6	X	2	5.0	8.5	10.1	I-2348454-3
4	X	1	2.5	6.0	7.6	I-2348454-2
POS	KEY	n	A	B	C	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05DEC2018 FISHER.ZHU	TE Connectivity			
DIMENSIONS: 単位: 耗 mm		CHK 05DEC2018 RICK.BIAN				
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5° 0-PLC ± 1-PLC ±0.3 2-PLC ±0.10 3-PLC ±0.001 4-PLC ±0.0001 ANGLES ± FINISH 仕上 -		APVD 05DEC2018 RICK.BIAN	NAME 名称 DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS			
MATERIAL 材料 &material		PRODUCT SPEC 製品規格 108-78298	SIZE CAGE CODE DRAWING NO 番号 A300779 C-2348454			
		APPLICATION SPEC 取付適用規格 114-5377	RESTRICTED TO			
		WEIGHT -	RESTRICTED CUSTOMER			
			SCALE 4:1 SHEET 1 OF 3 REV A			

THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
© COPYRIGHT 20 BY Tyco Electronics Japan G.K. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN APVD
				SEE SHEET 1 OF 3		



6POS(X-KEY):1-2348454-3

8POS(X-KEY):1-2348454-4










4POS(X-KEY):1-2348454-2



SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 05DEC2018 FISHER.ZHU	 TE Connectivity		
DIMENSIONS: mm		CHK 05DEC2018 RICK.BIAN			
		APVD 05DEC2018 RICK.BIAN	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS		
		PRODUCT SPEC 108-78298	SIZE A3	CAGE CODE 00779	DRAWING NO C-2348454
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC 114-5377	RESTRICTED TO		
MATERIAL &material		WEIGHT -	SCALE 4:1		
		FINISH -	SHEET 2 OF 3		
			REV A		

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
	-			SEE SHEET 1 OF 3			



10POS(X-KEY):1-2348454-5

12POS(X-KEY):1-2348454-6

16POS(X-KEY):1-2348454-8

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN FISHER.ZHU 05DEC2018	TE Connectivity			
DIMENSIONS: mm		CHK RICK.BIAN 05DEC2018				
		APVD RICK.BIAN 05DEC2018	NAME DYNAMIC D1200D 2.5mmPITCH HDR ASSY (V-TYPE) TIN PLATING 4-20POS			
		PRODUCT SPEC 108-78298				
MATERIAL &material		APPLICATION SPEC 114-5377	SIZE A300779			
		WEIGHT -				
FINISH -		RESTRICTED CUSTOMER		SCALE 4:1	SHEET 3 OF 3	REV A