


Technical specification:

Rated voltage: 3pos 4pos
IEC 61076-2-104 60 V 30 V

Current rating: 3 A bei 40°C
IEC 61076-2-104

Insulation resistance: $\geq 100 \text{ M}\Omega$
IEC 60512

Pollution degree: 3/2
IEC 60664-1

Degree of protection: IP 67, in mated condition
IEC 60529

Temperature range: -30°C ... +85°C
IEC 60664-1

Mating cycles: ≥ 100
IEC 60512-9a

Materials:

Contact: CuZn

Contact plating: Nickel, gold plated

Contact carrier: PA, UL 94

Socket housing: CuZn, nickel plated

Part no:	Description:	Pos	
42-01008	SAL - 8 - ESVM3 - L	3	
42-01009	SAL - 8 - ESVM4 - L	4	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	Index: b 02.03.11 fro Ä3914 Data sheet revised	dim. in mm	
		date	name
		drawn 15.10.08	Fromm
		appd. 15.10.08	Mankopf
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			

title:	Male socket M8x1 with soldering version
dwg no:	42K1A112
part no:	