



PLUG		RECEPTACLE		PLUG: WB40PR8
				RECEPTACLE: WB40SD6
				XXXXXXXXXX
SERIES				
WB 2 row, right angle, plug, with mounting ears		WB 2 row, straight, receptacle, with mounting ears		
SIZE				
20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132		20, 30, 40, 50, 60, 70, 80, 90, 100, 110, 128, 132		
CONTACTS				
TYPE CONTACTS/TERMINATIONS:		TYPE CONTACTS/TERMINATIONS:		
PR8	Pin, right angle, dip solder, .125"	SD6	Socket, straight, dip solder, .095"	
		SD9	Socket, straight, dip solder, .140"	
		SD12	Socket, straight, dip solder, .190"	
		SD19	Socket, straight, dip solder, .300"	
HARDWARE				
STYLE OF HARDWARE: (See WB-9)		STYLE OF HARDWARE: (See WB-9)		
K*_*	Integral keying guides, polarized	K*_*	Integral keying guides, polarized	
KY*_*	Stainless steel keying guides, polarized	KY*_*	Stainless steel keying guides, polarized	
JMM	2 stainless steel fixed jackscrews	JTFF	2 stainless steel turning jackscrews	

DIMENSIONS					
SIZE	A	B	C	D	E
20	1.150	.900	.450	1.030	.750
30	1.400	1.150	.700	1.280	1.000
40	1.650	1.400	.950	1.530	1.250
50	1.900	1.650	1.200	1.780	1.500
60	2.150	1.900	1.450	2.030	1.750
70	2.400	2.150	1.700	2.280	2.000
80	2.650	2.400	1.950	2.530	2.250
90	2.900	2.650	2.200	2.780	2.500
100	3.150	2.900	2.450	3.030	2.750
110	3.400	3.150	2.700	3.280	3.000
128	3.850	3.600	3.150	3.730	3.450
132	3.950	3.700	3.250	3.830	3.550