

## SUMMARY

### # Wires

Low voltage 8



*Image is for illustrative purpose only*

|                  |                                                                     |
|------------------|---------------------------------------------------------------------|
| Series           | 1B                                                                  |
| Termination type | Male solder                                                         |
| IP rating        | 50                                                                  |
| AWG wire size    | 30.00 - 22.00                                                       |
| Cable Ø          | 5.30 - 6.20 mm                                                      |
| Status           | active                                                              |
| Matching parts   | <a href="#">EGC.1B.308.CLL</a><br><a href="#">PHC.1B.308.CLLD62</a> |

### Download

[Request a quote](#)  
[Eplan](#)  
[Catalog](#)  
[See video assembly instructions](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                                                                               |
|-------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Shell Style/Model | FG*: Straight plug, cable collet                                                                                              |
| Keying            | 2 keys (alpha=90, plug: male contacts, receptacle: female contacts)                                                           |
| Housing Material  | Brass (chrome plated [SAE AMS 2460]) shell and collet nut, nickel plated [SAE AMS QQ N 290] brass latch sleeve and mid pieces |
| Weight            | 15.26 g                                                                                                                       |

### Performance

|               |                           |
|---------------|---------------------------|
| Configuration | 1B.308 : 8 Low Voltage    |
| Insulator     | L: PEEK (UL 94 / V-0/1.5) |
| Rated Current | 5 Amps                    |

### Specifications


Contact Type: Solder  
Contact Dia.: 0.7 mm (0.028in)  
Bucket Dia.: 0.8 mm (0.031in)  
Max. Stranded Conductor: 0.34 mm<sup>2</sup> (AWG 22)  
Max. Conductor: 0.34 mm<sup>2</sup> (AWG 22)  
R (max): 6.1 mOhm  
Vtest (contact-shell): 1150 V (AC), 1630 V (DC)  
Vtest (contact-contact): 950 V (AC), 1340 V (DC)

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Others

- Endurance (Shell): 5000
- Temp (min / max): -55° C / +250° C
- Humidity (max): <=95% [at 60 deg C / 140 F]
- Vibration: 15 g [10 Hz - 2000 Hz]
- Shock Resistance: 100 g [ 6 ms]
- Climatical Category: 50/175/21
- Shielding (min): 75 dB (10 MHz)
- Shielding (min): 40 dB (1 GHz)
- Salt Spray Corrosion: >1000 hr

DRAWINGS



Dimensions

|     | A    | L    | M    | S1   | S2   |
|-----|------|------|------|------|------|
| mm. | 12   | 43   | 32   | 10   | 9    |
| in. | 0,47 | 1,69 | 1,26 | 0,39 | 0,35 |

RECOMMENDED BY LEMO

Tools

Spanner wrench: [DCD.1B.015.PA090](#)

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Cables

|                    |               |        |                                                                                     |
|--------------------|---------------|--------|-------------------------------------------------------------------------------------|
| CMN.08.T22.059QGC  | TPR           | Grey   |                                                                                     |
| CMN.08.T22.059QGZE | TPR (medical) | Grey   |  |
| 16080              | PVC           | Grey   |                                                                                     |
| 180240             | PVC           | Black  |  |
| 180260             | PVC           | Black  |  |
| 335991             | PVC           | Black  |   |
| 42265              | PVC           | Yellow |                                                                                     |
| 80140              | PVC           | Grey   |  |

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.