


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	DIMENSIONS in. [mm]		
		L ± .02 [0,51]	B DIA. ± .01 [0,25]	C ± .01 [0,25]
ES18B	#22-18 [0,5-1,0]	.62 [15,7]	.14 [3,6]	.032 [0,81]
ES14B	#16-14 [1,5-2,5]	.62 [15,7]	.16 [4,1]	.032 [0,81]
ES10B	#12-10 [4,0-6,0]	.63 [16,0]	.22 [5,6]	.040 [1,02]

NOTES:


- USED FOR:
 - SOLID OR STRANDED COPPER WIRE
 - 302°F [150°C] MAX TEMPERATURE RATING
 - 2000V MAX VOLTAGE
- INSTALLATION TOOLS:
 - UL LISTED AND CSA CERTIFIED:
CT-100A, CT-200, CT-600A (CT-570CH),
CT-1570, CT-2500 (CT-2570CH)
 - PANDUIT APPROVED: CT-160, CT-260
- WIRE STRIP LENGTH: 9/32" ^{+1/32}₋₀ [7,1mm ^{+0,8}₋₀]
- MATERIAL: COPPER, TIN PLATED
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED
587H
E52164



CERTIFIED
LR31212

								TITLE				STRONGHOLD BUTT SPLICE NON-INSULATED, BUTTED SEAM #22-10 AWG			
												CUSTOMER DRAWING			
								ITEM REVISION NAME				00123SHB/00			
								DATASET FILE NAME				00123SHB_DC/00A			
								UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.13] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION				MATERIAL:		SEE NOTES	
												DRAWING NUMBER:			
00	10.5.17	TMR	JHNU	RGB	DRAWING RELEASED		00123SH								
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY		DATE	CHK	SCALE	SHEET 1 OF 1		SIZE
								TMR		10.5.17	JHNU	N.T.S			A