

SPECIFICATIONS:

MATERIALS:

HOUSING:

PBT, UL94 V-0, BLACK

CONTACTS:

GOLD PLATED BRASS

(SEE P/N KEY BELOW)

NUT:

NICKEL PLATED BRASS

SHELL:

NICKEL PLATED BRASS

ORING:

EPDM, BLACK

ELECTRICAL:

RATED CURRENT: 4A

250V





RATED VOLTAGE: 100 MOhms MIN.

CONTACT RESISTANCE: 10 mOhms MAX.


ENVIRONMENT:

OPERATING TEMPERATURE: -40°C TO +85°C

IP67



861-D04-113R00Y

3 = BRASS/NICKEL SHELL & NUT
S = STAINLESS STEEL SHELL & NUT1 = GOLD FLASH
4 = 10μ" GOLD

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE
THE PROPERTY OF NorComp AND SHALL NOT
BE REPRODUCED, COPIED OR USED AS THE
BASIS FOR THE MANUFACTURE OR SALE OF
APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

07/26/2016

UNITS = inch[mm]

DO NOT SCALE FROM DRAWING

NorComp

SCALE:	1	OF	REV
NTS	1	1	3
DWG NO.			
			861-D04-113R00Y