

CT3753

Banana Plug Test Lead

Datasheet

UL Listed 4mm Straight Banana Plug to Right-Angle Banana Plug...

Description

UL Listed 4mm Straight Sheathed Banana Plug to Right-Angle Sheathed Banana Plug Test Lead. Highly flexible silicone jacketed test lead wire.

- Banana Contact: BeCu, Nickel Plt.
- Available in 2 standard lengths



Technical data subject to change.

© Cal Test Electronics 2018.

caltestelectronics.com



All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

Specifications

UL Rating	1,000 V CAT III
Current, Max	10 A
Jacket Material	Silicone
Conductor Area	0.87 mm ²
Wire Gauge, AWG	18 AWG
Stranding (# x dia.)	168 x 0.07 mm
Jacket OD	3.7 mm (0.146")
Temperature (degrees)	-20 to +80C
RoHS (2011/65/EU)	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: caltestelectronics.com