



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		A1	REVISED PER ECO-15-006065	22APR2015	NK	RH

D


C

B


A



P.C. MOUNTING



VERTICAL LAYOUT



SPECIFICATIONS

MECHANICAL LIFE: 30,000 MAKE AND BREAK CYCLES.
CONTACT RESISTANCE: 20 mΩ MAX. INITIAL @ 2-4VDC
100mA FOR GOLD PLATED CONTACTS.
INSULATION RESISTANCE: 1,000MΩ MIN.
DIELECTRIC STRENGTH: 1,000V RMS MIN @SEA LEVEL.
OPERATING TEMPERATURE: -30°C TO 85°C.
CONTACT RATING: 0.4VA MAX @ 20V MAX (AC OR DC)

VERTICAL, SMT	PLASTIC	2-1	2-3	(ON)-ON	2	1	TBS2TBA1MZRES	2267131-6
RIGHT ANGLE, SMT	BRASS	2-1	2-3	(ON)-ON	2	1	TBS2T2A1MTRES	2267131-5
VERTICAL, SMT	PLASTIC	2-1	2-3	ON-ON	2	1	TBS1TBA1MZRES	2267131-4
RIGHT ANGLE, SMT	PLASTIC	2-1	2-3	ON-ON	2	1	TBS1TBA1MTRES	2267131-3
VERTICAL, SMT	BRASS	2-1	2-3	ON-ON	2	1	TBS1T2A1MZRES	2267131-2
RIGHT ANGLE, SMT	BRASS	2-1	2-3	ON-ON	2	1	TBS1T2A1MTRES	2267131-1
TERMINATION	ACTUATOR	POS 2	POS 1	FUNCTION	THROWS	POLES	TE DESCRIPTIVE PART NUMBER	TE PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -
1 PLC ± 0.40[.015]
2 PLC ± 0.25[.010]
3 PLC ± -
4 PLC ± -
ANGLES ± 5°
FINISH

DWN NAGALAKSHMI K 20JUN2014
CHK HILL RYAN 20JUN2014
APVD HILL RYAN 20JUN2014
PRODUCT SPEC
APPLICATION SPEC
WEIGHT -
CUSTOMER DRAWING

TE Connectivity

NAME
SUBMINIATURE TOGGLE SWITCH,
SEALED, SMT

SIZE A2
CAGE CODE -
DRAWING NO C-2267131
SCALE 1:1
SHEET 1 OF 2
REV A1

RESTRICTED TO

2267131

A


4

3


2

1

LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
G	14			SEE SHEET 1	-	-



RIGHT ANGLE LAYOUT



P.C. MOUNTING

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN NAGALAKSHMI K 20JUN2014	TE Connectivity			
DIMENSIONS: mm [INCHES]		CHK HILL RYAN 20JUN2014				
	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.40[.015] 2 PLC ± 0.25[.010] 3 PLC ± - 4 PLC ± - ANGLES ± 5°		NAME HILL RYAN 20JUN2014			
			PRODUCT SPEC			
			APPLICATION SPEC			
MATERIAL		FINISH	WEIGHT	-	SIZE A2	CAGE CODE -
CUSTOMER DRAWING			SCALE	1:1	SHEET	2 OF 2
			REV	A1	RESTRICTED TO	