




ITEM #	PART #	QTY	DESCRIPTION	MATERIAL
1	AP-135-1	1	SHELL ASS'Y	GLASS FILLED NYLON & 303 SS
2	AP-125-6	1	INSERT ASS'Y	DIALLYPHTHALATE, TYPE SDGF & GOLD PLATED BRASS
3	AP-105-5	1	STRAIN RELIEF	NYLON
4	AP-116-3	1	WASHER	RUBBER
5	AP-136-8	1	NUT ADAPTER	ALUMINUM, BLACK CHROME
6	AP-136-6	1	CLAMP SHIELD, OUTER	NICKEL PLATED BRASS
7	AP-136-5	1	CLAMP SHIELD INNER	NICKEL PLATED BRASS
8	AP-116-8	1	BUSHING	RUBBER
9	AP-116-2	1	WASHER	STAINLESS STEEL
10	AP-116-4	1	SPRING	302 STAINLESS STEEL
11	AP-116-6	1	STUD	ANODIZED ALUMINUM ALLOY



NOTES:
1) UNLESS OTHERWISE SPECIFIED, CONNECTOR MEETS ALL
GENERAL REQUIREMENTS & SPECIFICATIONS OF MIL-C-55116

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION OF NEXUS, INCORPORATED AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR ANY PURPOSE WITHOUT THE WRITTEN CONSENT OF NEXUS.

					DWN.BY MNF	DATE 2/4/97	MATERIAL	
					CHECKED BY L SMITH	DATE 9/9/97	FINISH	
					APPR.BY L SMITH	DATE 9/9/97	WEIGHT	SCALE = 1.00 :1
					UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES &/OR [mm] TOLERANCES: DECIMAL: ±.XX[X.X] ±.01[0.3] ±.XXX[X.XX] ±.003[0.08] FRACTION: ±X/X ± 1/64 ANGLES: ±X ±.5		TITLE AUDIO PLUG	
							DO NOT SCALE DWG.	SHEET 1 OF 1
							SIZE C	DWG. NO. AP-135
B	ADD P/N'S IN P/L	101	2/25 2011	HR				
A	REVISED & REDRAWN ON CAD	0259	2/24 1997	LS				
LET.	REVISION	CN #	DATE	CHK				