



CQB60W-110S SERIES

60 WATT

DC-DC CONVERTERS



FEATURES

- * 60W Isolated Output
- * Efficiency to 92%
- * Low No Load Power Consumption
- * 4:1 Input Range
- * Regulated Outputs
- * Remote On/Off
- * Over Temperature/Voltage/Current Protection
- * Continuous Short Circuit Protection
- * Quarter Brick Size Meet Industrial Standard
- * UL60950-1 (Basic Insulation) Approval
- * Meets EN50155 with External Circuits
- * Shock & Vibration Meets EN50155 (EN61373)
- * Fire & Smoke Meets EN45545-2
- * 4000m Operating Altitude
- * Safety Meets IEC/EN/UL 62368-1



MODEL NUMBER	INPUT VOLTAGE	OUTPUT VOLTAGE	OUTPUT CURRENT		INPUT CURRENT		% EFF.	CAPACITOR LOAD MAX.
			MIN.	MAX.	NO LOAD	FULL LOAD		
CQB60W-110S05	43-160 VDC	5 VDC	0 mA	12 A	5 mA	600 mA	91	6800 μ F
CQB60W-110S12	43-160 VDC	12 VDC	0 mA	5 A	5 mA	593 mA	92	3300 μ F
CQB60W-110S15	43-160 VDC	15 VDC	0 mA	4 A	5 mA	606 mA	90	3300 μ F
CQB60W-110S24	43-160 VDC	24 VDC	0 mA	2.5 A	5 mA	606 mA	90	1200 μ F
CQB60W-110S28	43-160 VDC	28 VDC	0 mA	2.14 A	5 mA	606 mA	90	1200 μ F
CQB60W-110S48	43-160 VDC	48 VDC	0 mA	1.25 A	5 mA	613 mA	89	470 μ F

NOTE:

1. Nominal Input Voltage 110VDC

