




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL DRAWING	12NOV2021	C.C	I.Y
	A1	ECR-22-136442	12APR2022	S.T	Z.Z
	A2	ECR-22-153884	19SEP2022	S.T	Z.Z



- 1 MATERIAL: COPPER ALLOY
2. BULK PACKAGED



2387549-4	CRIMP ANVIL - 150SQ	Ø25.6	24.5	25.5
2387549-3	CRIMP ANVIL - 120SQ	Ø23.1	22.2	23.0
2387549-2	CRIMP ANVIL - 95SQ	Ø20.4	19.5	20.3
2387549-1	CRIMP ANVIL - 70SQ	Ø17.4	16.7	17.3
PART NO.	DESCRIPTION	DIA.A	MIN.	MAX.
			CABLE O.D.	

© 2021 TE Connectivity. All Rights Reserved.

DIMENSIONS:		DWN	12NOV2021	MATERIAL	1	FINISH	
mm		CHK	12NOV2021				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		J.L.I	12NOV2021				
±0.3		APVD	12NOV2021	NAME CRIMP ANVIL HVP-HD1400			
0 PLC ±		I.YIN					
1 PLC ±0.1		PRODUCT SPEC	108-160407	SIZE A 4 CAGE CODE 00779 DRAWING NO C-2387549			
2 PLC ±0.01		APPLICATION SPEC	114-160223/160418				
3 PLC ±0.001		WEIGHT		RESTRICTED TO -			
4 PLC ±0.0001							
ANGLES ±		CUSTOMER DRAWING		SCALE	2:1	SHEET	1 OF 1
				REV A2			