





APPROVED: _____
 DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	6/2/05	
A		REDRAWN	10/5/11	
B		UPDATE TOLERANCE	1/29/21	LH/YC



SPECIFICATIONS:

Material:

Insulator: Nylon, rated UL 94V-0

Insulator color: White

Contacts: Phosphor Bronze

Plating:

Tin over Copper underplate overall

Electrical:

Voltage rating: 250 V

Current rating: 2.5 Amp max.

Contact resistance: 20 mohms max. initial

Insulation resistance: 5000 Mohms min.

Dielectric withstanding voltage: 1,500 VAC for 1 minute

Mechanical:

Recommended PCB thickness: 0.062" (1.57mm)

Temperature Rating:

0°C to +75°C

Environmental:

Lead free, RoHS compliant



Positions: 02 thru 25

A = .100 [2.54] x No. of Spaces + .096 [2.44]

B = .100 [2.54] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES HOLES <table><tr><td>.X</td><td>± .10</td><td>Ø.X</td><td>±.10</td></tr><tr><td>.XX</td><td>± .020</td><td>Ø.XX</td><td>±.015</td></tr><tr><td>.XXX</td><td>± .015</td><td>Ø.XXX</td><td>±.010</td></tr></table>		.X	± .10	Ø.X	±.10	.XX	± .020	Ø.XX	±.015	.XXX	± .015	Ø.XXX	±.010	 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710	
		.X	± .10	Ø.X	±.10										
		.XX	± .020	Ø.XX	±.015										
		.XXX	± .015	Ø.XXX	±.010										
TITLE .100 [2.54] PCB CONNECTOR BOARD HOOKS, SIDE ENTRY															
		SIZE X		PART NO. PCE-B-XX		REV. B									
				REF: S00123T		SCALE: NTS	SHEET 1 OF 1								
APPROVALS		DATE													
DRAWN	SS	6/2/05													
CHECKED															
APPROVED															