

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.			THIRD ANGLE PROJECTION 		SCALE FULL		
CHARACTERISTICS			ELECTRICAL DATA			DO NOT SCALE PRINT	
OPERATING FORCE ——— 6-12 LB			CONTACT ARRANGEMENT			TOLERANCES	
FULL OVERTRAVEL FORCE ——— 30 LB MAX			2X SPDT			APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE 1	
RELEASE FORCE ——— 4 LB MIN			LOAD	28 VDC		DIM. TOL. DIM. TOL. mm mm/in in mm/in	
PRETRAVEL ——— .040 MAX				100,000 FT.		NO PLACES X 1/04 ONE PLACE X,X 0.47/016 X X 0.87/03 TWO PLACES X,X,X 0.157/.008 X,X 0.38/.015 THREE PLACES X,X,X,X 0.13/.005 ANGLES	
DIFFERENTIAL TRAVEL ——— .020 MAX				RES	5	5	DIMETRIC US CUSTOMARY
OVERTRAVEL ——— .250 MIN				IND	3	3	
			MOTOR	4	4		
			LAMP			WEIGHT 12 OZ MAX	