


| SIGN                                           | DATE     | DESCRIPTION     | APPROVER |
|------------------------------------------------|----------|-----------------|----------|
| △                                              | 04/07'10 | Add the 2P mark | RUNNER   |
| THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!! |          |                 |          |




Dimension

|       |            |
|-------|------------|
| DIM A | N×5.0+0.10 |
| DIM B | ( N-1)×5.0 |

N=Number of poles

| POLES   | TOL   |
|---------|-------|
| 2p-6p   | ±0.15 |
| 7p-12p  | ±0.25 |
| 13p-16p | ±0.35 |
| 17p-24p | ±0.40 |



Material



- Item a Terminal body:Thermoplastic ( UL94V-0 )
- Item b Terminal body:Thermoplastic ( UL94V-0 )
- Item c Terminal lever:Thermoplastic ( UL94V-0 )
- Item d Wire guard:Stainless Steel
- Item e Female contact:PhBz ( CuSn ) Tin plated
- Item f With flange screw:Steel Zinc plating M2.5 solt "+/-" type

Electrical cULus



- Voltage rating:300V
- Current rating:10A
- Solid wire(AWG):12-26
- Stranded wire(AWG):12-26
- Wire strip length:9-10mm
- Withstanding Voltage:1.6KV
- Operating temperature:-40°C to +115°C
- Safety Approval: cULus

H4 xx 70 x D xxxx G

|                |         |                                                                        |              |
|----------------|---------|------------------------------------------------------------------------|--------------|
| 02 2 CONTACTS  | 0 Black | 0000 Standard @ Logo                                                   | RoHS         |
| 03 3 CONTACTS  | 5 Green | 000A Standard ANY Logo                                                 | Pb<40,000ppm |
| ... ..         | 6 Blue  | Any special item by customer request, please contact sales department. |              |
| 24 24 CONTACTS | 8 Grey  |                                                                        |              |



SECTION A-A



|                                                                                                                                                                                         |                                                 |                      |                    |               |             |            |           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------|----------------------|--------------------|---------------|-------------|------------|-----------|
| ANYTEK                                                                                                                                                                                  |                                                 |                      |                    | CUSTOMER COPY |             |            |           |
| ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD |                                                 |                      |                    |               |             |            |           |
| TITLE                                                                                                                                                                                   | H4 5.0 Series hook on back side ( With flange ) |                      |                    |               |             |            |           |
| PART NO.                                                                                                                                                                                | H4xx70xDxxxxG                                   |                      |                    | DWG NO.       | 8H40104     |            |           |
| APPROVED                                                                                                                                                                                | CHECKED                                         | DESIGNED             | DRAWN              | CUST NO.      | <div></div> |            | Tolerance |
|                                                                                                                                                                                         |                                                 | Runner<br>2010.04.07 | Tony<br>2009.03.12 |               |             |            | X. ±0.50  |
|                                                                                                                                                                                         |                                                 |                      |                    | <div></div>   | UNIT: mm    | X.X ±0.30  |           |
|                                                                                                                                                                                         |                                                 |                      |                    | SHEET: 01/01  | SCALE: NONE | X.XX ±0.10 |           |
|                                                                                                                                                                                         |                                                 |                      |                    |               | REV.: C     | X* ±1*     |           |