





Aries Low Cost, Quick Turn QFP Prototyping Adapters

FEATURES

- Mates common QFP packages to standard breadboard and breakout boards for rapid and easy prototyping
- Panelized adapters available upon request

GENERAL SPECIFICATIONS

- BOARD MATERIAL: 0.062 [1.58] thick FR-4, UL 94V-0 with 1/2-oz. Cu traces
- PIN INSULATOR: Polyester, UL 94V-0
- PINS: Brass 360 1/2-hard per UNS C36000 ASTM-B16-00
- PIN PLATING: Au Flash
- OPERATING TEMPERATURE: -55°C to +125°C



ORDERING INFORMATION

Indicate desired P/N



Pads	Device Body Size inch [mm]	Dim. "A" inch [mm]	Dim. "B" inch [mm]	Dim. "C" inch [mm]	Dim. "D" inch [mm]	Dim. "F" inch [mm]	Dim. "e" inch [mm]	P/N
32	0.197 x 0.197 [5 x 5]	0.244 [6.2]	0.244 [6.2]	0.012 [0.30]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-32
32	0.276 x 0.276 [7 x 7]	0.339 [8.6]	0.339 [8.6]	0.016 [0.40]	1.70 [43.18]	1.50 [38.10]	0.031 [0.80]	LCQT-QFP0.8-32
40	0.197 x 0.276 [5 x 7]	0.244 [6.2]	0.323 [8.2]	0.012 [0.30]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-40
40	0.276 x 0.276 [7 x 7]	0.323 [8.2]	0.323 [8.2]	0.016 [0.40]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-40-1
44	0.394 x 0.394 [10 x 10]	0.472 [12]	0.472 [12]	0.020 [0.50]	1.70 [43.18]	1.50 [38.10]	0.031 [0.80]	LCQT-QFP0.8-44
52	0.276 x 0.394 [7 x 10]	0.323 [8.2]	0.441 [11.2]	0.012 [0.30]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-52
52	0.394 x 0.394 [10 x 10]	0.472 [12]	0.472 [12]	0.016 [0.40]	1.50 [38.10]	1.30 [33.02]	0.026 [0.65]	LCQT-QFP0.65-52
60	0.276 x 0.394 [7 x 10]	0.323 [8.2]	0.441 [11.2]	0.012 [0.30]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-60
64	0.394 x 0.394 [10 x 10]	0.441 [11.2]	0.441 [11.2]	0.012 [0.30]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-64
64	0.472 x 0.472 [12 x 12]	0.559 [14.2]	0.559 [14.2]	0.016 [0.40]	1.50 [38.10]	1.30 [33.02]	0.026 [0.65]	LCQT-QFP0.65-64
64	0.551 x 0.551 [14 x 14]	0.630 [16]	0.630 [16]	0.020 [0.50]	1.70 [43.18]	1.50 [38.10]	0.031 [0.80]	LCQT-QFP0.8-64
80	0.472 x 0.472 [12 x 12]	0.520 [13.2]	0.520 [13.2]	0.012 [0.30]	1.50 [38.10]	1.30 [33.02]	0.020 [0.50]	LCQT-QFP0.5-80
80	0.551 x 0.551 [14 x 14]	0.630 [16]	16 [0.016]	0.016 [0.40]	1.50 [38.10]	1.30 [33.02]	0.026 [0.65]	LCQT-QFP0.65-80
80	0.551 x 0.787 [14 x 20]	0.638 [16.2]	0.874 [22.2]	0.020 [0.50]	1.70 [43.18]	1.50 [38.10]	0.031 [0.80]	LCQT-QFP0.8-80

• ALL DIMENSIONS: INCHES [MILLIMETERS] • ALL TOLERANCES: ±0.005 [0.13] UNLESS OTHERWISE SPECIFIED • CONSULT FACTORY FOR OTHER SIZES AND CONFIGURATIONS

CUSTOMIZATION: ARIES SPECIALIZES IN CUSTOM DESIGN AND PRODUCTION. SPECIAL MATERIALS, PLATINGS, SIZES, AND CONFIGURATIONS CAN BE FURNISHED, DEPENDING ON QUANTITY.

ARIES RESERVES THE RIGHT TO CHANGE PRODUCT GENERAL SPECIFICATIONS WITHOUT NOTICE

PRINTOUTS OF THIS DOCUMENT MAY BE OUT-OF-DATE AND SHOULD BE CONSIDERED UNCONTROLLED



ARIES
ELECTRONICS, INC.

2609 Bartram Road • Bristol, PA 19007-6810 USA
TEL 215-781-9956 • FAX 215-781-9845
WWW.ARIESELEC.COM • INFO@ARIESELEC.COM

19001
Rev. 1.1
1 of 1