

DIALIGHT PART NUMBER	DIM "A"	TERMINAL TYPE	COLLAR & FLANGE NUT FINISH
508-7438-504	.865 [21,74]	FIG. 1	BLACK ANODIZE
508-7438-604	.865 [21,74]	FIG. 1	CLEAR ANODIZE
508-7445-504	.942 [23,92]	FIG. 1	BLACK ANODIZE
508-7445-604	.942 [23,92]	FIG. 1	CLEAR ANODIZE
508-7538-504	.834 [21,18]	FIG. 2	BLACK ANODIZE
508-7538-604	.834 [21,18]	FIG. 2	CLEAR ANODIZE
508-7545-504	.920 [23,37]	FIG. 2	BLACK ANODIZE
508-7545-604	.920 [23,37]	FIG. 2	CLEAR ANODIZE
508-8738-504	.848 [21,54]	FIG. 3	BLACK ANODIZE
508-8738-604	.848 [21,54]	FIG. 3	CLEAR ANODIZE
508-8745-504	.934 [23,72]	FIG. 3	BLACK ANODIZE
508-8745-604	.934 [23,72]	FIG. 3	CLEAR ANODIZE




FIG.1 - SOLDER BLADE TERMINALS

NOTES:

- 1. DIALIGHT PART NUMBERS: 508-74XX-504, 508-74XX-604, 508-75XX-504, 508-75XX-604, 508-87XX-504 & 508-87XX-604.
- 2. MAXIMUM PANEL THICKNESS: .156"
- 3. RECOMMENDED MOUNTING HOLE SIZE: .380±.002".

REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
A	—	NEW RELEASE	AJF	KLJ	NO	12-20-10




FIG.2 - SOLDER CUP TERMINALS




FIG.3 - TURRET TERMINALS

THIS DRAWING AND THE CONTENTS HEREIN ARE CONFIDENTIAL AND THE SOLE PROPERTY OF DIALIGHT. REPRODUCTION OF THIS DRAWING OR CONSTRUCTION OF ANY PARTS WITHIN THIS DRAWING ARE FORBIDDEN WITHOUT THE WRITTEN CONSENT OF DIALIGHT.				
SCALE: 4.000		DRAWING NUMBER C-17895		REV A
ALL DIM'S IN: INCHES (MM)				
TOLERANCES: UNLESS OTHERWISE SPECIFIED		TITLE 508 SERIES DATALAMP HOLDER		
FRACTIONS: ±1/64				
DECIMALS (.XX): ±.01				
DECIMALS (.XXX): ±.005				
DECIMALS (.XXXX): ±.0005				
ANGLES: ±1°		MATERIAL		
FINISH:		Dialight 1501 ROUTE 34 SOUTH FARMINGDALE, NJ 07727		
FSCM 83330		SHEET 1 OF 1 FAMILY TABLE:		