

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT - By -

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


N

ECR-13-000998

11FEB2013

PK

HS



1 TIN PL .000150 MIN THK
MIL-T-10727

2 PART NO: 324464; .146 LB.
PART NO: 1-324464-0; .146 LB.
PART NO: 2-324464-1; .164 LB.
PART NO: 2-324464-2; .164 LB.

3 .045 MAX BURR ALLOWED INSIDE THE WIRE
BARREL ID IN AREA OF SIGHT HOLE.

.91	1.16	2.29	CLEANED	325-375 MCM	COPPER ASTM-B-75 ANNEALED	2-324464-2
			△			2-324464-1
.91	.91	2.06	CLEANED			1-324464-0
			△			324464
"C"	"B"	"A"	FINISH	WIRE RANGE	MATERIAL	PART No

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN DK SCHRUM 4/24/89

CHK MS FEHER 4/24/89

APVD WJ VOCKROTH 11/8/89

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

TE

TE Connectivity

SPLICE, BUTT, AMPPOWER
WIRE SIZE: 350 MCM

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C=324464

SCALE

2:1

SHEET


1 OF 1

REV

N

DIMENSIONS:

INCHES

MATERIAL
SEE TABLETOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -

FINISH
SEE TABLE