




SIGN	DATE	DESCRIPTION	APPROVER
△	07/22`13	update the drawing	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



Material

- Item a Clamp: Brass(Cuzn) Ni plated
- Item b Terminal screw: Steel Zinc plating;"- "slot type
- Item c Female contact: PhBz
- Item d Terminal(housing): Thermoplastic (UL94V-0)

Electrical

- Voltage rating: 150VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 16-28
- Stranded wire(AWG): 16-28
- Torque(Lb-In): 1.1
- Screw: M2
- Wire strip length: 5-6mm
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Safety Approval: 
- Critical dimension: 

EHxx21x0xxxxG

Poles		G RoHS compliant (lead<4%)
02 2Contacts		In copper Alloy
03 3Contacts		0000 Standard @ Logo
...		000A Standard ANY Logo
24 24Contacts	0 Black (RAL9005)	Any special item by customer request, please contact sales department.
	2 Red (RAL3001/D)	
	3 Orange(RAL2011/P)	
	4 Yellow(RAL1018/A)	
	5 Green(RAL6018/T)	
	6 Blue (RAL5015/A)	
	8 Grey(RAL7035/D)	
	9 White(RAL1102)	
	C Green(RAL6018/U)	

N = Number of poles
Dim A=Nx3.5
Dim B=(N-1)x3.5

	Dim A	Dim B
2-6p	±0.15	±0.15
7-12p	±0.20	±0.20
13-18p	±0.25	±0.25
19-24p	±0.30	±0.25

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		EH - 3.5mm Series				DWG NO.		8EH0001	
PART NO.		EHxx21x0xxxxG				CUST NO.			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance	
		Chen Bo 09/12 '13	Chen Bo 09/12 '13			UNIT: mm	X.	±0.50	
				SHEET: 01/01		SCALE: NONE	X.X	±0.30	
						REV.: D	X.XX	±0.10	
							X°	±1°	