

● SHORT CIRCUIT U LINKS

The short circuit U link is a complementary component to the 20-way fixed connector and can be used to make shunts. It is fitted with a rear-mounted 2 mm dia. socket.

CHARACTERISTICS

– Current rating max	: 7 A (at 20°C)
– Dielectric withstanding voltage	: 2 000 V rms 50 Hz
– Operating voltage	: 500 V rms 50 Hz
– Insulation resistance	: $\geq 5\,000\text{ M}\Omega$
– Mechanical endurance	: > 10 000 matings
– Operating temperature	: - 40°C + 70°C

► Packaging : 100 pieces of the same part number.

Part number	Dimensions (12 mm between axes)
R 644 543 000 / Blue R 644 543 001 / Red R 644 543 002 / Green R 644 543 003 / Black R 644 543 004 / Yellow	

Part number	Dimensions (6 mm between axes)
R 644 543 020* / Blue R 644 543 021* / Red R 644 543 022* / Green R 644 543 023* / Black R 644 543 024* / Yellow	

* Made to order product, please consult Radiall for price and delivery