



"3 in 1" Combi-Terminal Switch



*"3 in 1" combi-terminals function
as .250 Quick Connect, Solder Lug
or Screw Terminals.*

In an effort aimed at reducing distributor inventory and increasing flexibility, Carling Technologies is pleased to introduce our new "Combi" terminal switches. These terminals function as both a .250 Quick Connect and Solder Lug terminal. In addition a screw and saddle clamp are included to provide a Screw Terminal option. This new offering is available on all full size Carling one to three pole rocker and toggle switches, and is a direct replacement for the discontinued Eaton 7800 series toggles with similar terminations.

Additional features include:

- UL, CSA approved
- Available with all circuits
- Parts provided in individual polybags
- Eliminates the need to stock three separate terminal configurations
- Available with standard #5 rating
(10A 250VAC 15A 125 VAC 3/4 HP 125-250 VAC)
- Additional ratings to 20A 125 VAC available
(consult factory for specifics)
- Full Choice of actuator colors and styles
- No additional lead-time

Product Availability:

- Samples and production orders are available

Product Bulletin #87R-1 April 18, 2002

For additional information on the "3 in 1"
Combi-Terminal Switch, please contact a Carling
Technologies Technical Customer Service Rep:

phone	(860) 793-9281
fax	(860) 793-9231
email	sales@carlingtech.com
internet	www.carlingtech.com
mail	Carling Technologies, Inc. 60 Johnson Avenue Plainville, CT 06062-1177



Carling Technologies™
Innovative Designs. Powerful Solutions.

"3 in 1" Combi-Terminal Rocker Switch Ordering Scheme

SINGLE POLE IN SINGLE POLE BASE

TILA57 - **1S** - **BL** - **FN**

1 2 3 1
Base Part Number Actuator Color Base Part Number

1 BASE PART NUMBER: SERIES / SINGLE POLE / CIRCUITRY / RATING 5 / TERMINATION³

RATING 5 = 10A 250 VAC, 15A 125 VAC, 3/4 HP 125-250 VAC¹

TIL-Series Rocker

single pole

circuit⁴

ON-NONE-OFF	TILA57
(ON)-NONE-OFF	TILA5H
ON-NONE-(OFF)	TILA5Y
ON-NONE-ON	TILB57
ON-NONE-(ON)	TILB5H
ON-OFF-ON	TILC57
ON-OFF-(ON)	TILC5H
(ON)-OFF-(ON)	TILC5Y

2 ACTUATOR STYLE

1S	Angular/Smooth Face Gloss
1C	Angular/Cross Serration Gloss
1F	Flatted/Smooth Face Gloss
1L	Angular/Longline Serration Gloss

3 ACTUATOR COLOR²

BL	Black
WH	White
RD	Red

4 BRACKET STYLE³

FN	Metal Snap-In
FN BLK	Black Metal Snap-In
FN SS	Stainless Steel Snap-In
FW	Wide Stainless Steel Snap-In

NOTES

Three and four pole switches also available. Consult factory for details.

¹ Rating appropriate for usage in low voltage DC applications. For additional rating requirements, consult factory.

² Custom colors are available, consult factory.

³ Additional terminations and bracket styles are also available. Consult factory for catalog number callout.

⁴ () - momentary



Carling Technologies™

Innovative Designs. Powerful Solutions.

"3 in 1" Combi-Terminal Rocker Switch Ordering Scheme

SINGLE OR DOUBLE POLE IN DOUBLE POLE BASE

TIGK57 - **6M** - **BL** - **WBL**

¹
Base Part Number

²
Actuator

³
Color

¹
Base Part Number

1 BASE PART NUMBER: SERIES / DOUBLE POLE BASE / CIRCUITRY / RATING 5 / TERMINATION⁹

RATING 5 = 10A 250 VAC, 15A 125 VAC, 3/4 HP 125-250 VAC⁷

TIG-Series Rocker

	single pole	double pole
circuit⁹		
ON-NONE-OFF	TIGA57	TIGK57
(ON)-NONE-OFF	TIGA5H	TIGK5H
ON-NONE-(OFF)	TIGA5Y	TIGK5Y
ON-NONE-ON	TIGB57	TIGL57
ON-NONE-(ON)	TIGB5H	TIGL5H
ON-OFF-ON	TIGC57	TIGM57
ON-OFF-(ON)	TIGC5H	TIGM5H
(ON)-OFF-(ON)	TIGC5Y	TIGM5Y

2 ACTUATOR STYLE

1S	Angular/Smooth Face Gloss ¹
1C	Angular/Cross Serrations Gloss ¹
1F	Flatted/Smooth Face Gloss ¹
1L	Angular/Longline Serrations Gloss ¹
6M	Curved/Smooth Face Matte ²
6S	Curved/Smooth Face Gloss ²
7S	Rounded Paddle/Smooth Face Gloss ¹

3 ACTUATOR COLOR⁸

BL	Black
WH	White
RD	Red

4 BRACKET STYLE⁸

NBL	Nylon Black
WBL	Watershedding Black ³
MBL	Marine Style Black ^{3,5}
FN	Metal Snap-In ⁴
FN BLK	Black Metal Snap-In ⁴
FN SS	Stainless Steel Snap-In ⁴
FW	Wide Stainless Steel Snap-In ⁴

NOTES

Three and four pole switches also available. Consult factory for details.

1 NBL, FN, & FW brackets only.

2 NBL, WBL, & MBL brackets only. With 6M actuator, brackets also will be matte finish.

3 6M & 6S actuators only

4 Not available with 6M & 6S actuators.

5 Consists of WBL bracket, neoprene seal, and dummy rivets at open holes. Consult factory for agency approval status.

6 Rating appropriate for usage in low voltage DC applications. For additional rating requirements, consult factory.

7 Custom colors are available, consult factory.

8 Additional terminations and bracket styles are also available. Consult factory for catalog number callout.

9 () - momentary



Carling Technologies™

Innovative Designs. Powerful Solutions.

"3 in 1" Combi-Terminal Toggle Switch Ordering Scheme

SINGLE POLE IN SINGLE POLE BASE

2FA52 - **73**

¹
Base Part Number

²
Actuator

1 BASE PART NUMBER: SERIES / SINGLE POLE / CIRCUITRY / RATING 5 / TERMINATION

RATING 5 = 10A 250 VAC, 15A 125 VAC, 3/4 HP 125-250 VAC²
F-Series Toggle

	single pole
circuit¹	
ON-NONE-OFF	2FA52
(ON)-NONE-OFF	6FA5H
ON-NONE-(OFF)	6FA5Y
ON-NONE-ON	2FB52
ON-NONE-(ON)	6FB52
ON-OFF-ON	2FC52
ON-OFF-(ON)	6FC5Y
(ON)-OFF-(ON)	6FC5H

2 BAT STYLE TOGGLE

unsealed	toggle length	bushing length
73	0.687	0.465
E3	2.000	0.465
sealed	toggle length	bushing length
78	0.687	0.465
E8	2.000	0.465

SINGLE AND DOUBLE POLE IN DOUBLE POLE BASE

2GK57 - **73**

¹
Base Part Number

²
Actuator

1 BASE PART NUMBER: SERIES / DOUBLE POLE BASE/ CIRCUITRY / RATING 5 / TERMINATION

RATING 5 = 10A 250 VAC, 15A 125 VAC, 3/4 HP125-250VAC²
G-Series Toggle

	single pole	double pole
circuit¹		
ON-NONE-OFF	2GA57	2GK57
(ON)-NONE-OFF	6GA5H	6GK5H
ON-NONE-(OFF)	6GA5Y	6GK5Y
ON-NONE-ON	2GB57	2GL57
ON-NONE-(ON)	6GB5H	6GL5H
ON-OFF-ON	2GC57	2GM57
ON-OFF-(ON)	6GC5H	6GM5H
(ON)-OFF-(ON)	6GC5Y	6GM5Y

2 TOGGLE

bat style

unsealed	toggle length	bushing length
73	0.687	0.465
D-3B-B	0.687	0.379
sealed	toggle length	bushing length
78	0.687	0.465

paddle style

unsealed	toggle length	bushing length
NBL3	0.687	0.465
sealed	toggle length	bushing length
NBL8	0.687	0.465
D-4B-B	0.687	0.379

NOTES

Additional ratings available. Consult factory for ordering information.
Three and four pole switches also available. Consult factory for details.

1 () - momentary

2 Rating appropriate for usage in low voltage DC applications. For additional rating requirements, consult factory.



Carling Technologies™

Innovative Designs. Powerful Solutions.