


SIGN	DATE	DESCRIPTION	APPROVER
△	04/25`11	Material is changed	Chen Bo
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material:

- Item ① Terminal housing: PA66 (UL94V-0)
- Item ② Male contact long pin: Brass, Tin plated
- Item ③ Male contact short pin: Brass, Tin plated
- Item ④ With flange nut: Brass, Nickel plated, M2.0

Electrical: cULus

- Voltage rating: 150V
- Current rating: 7 A
- Withstanding Voltage: 1.3KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: 



SECTION A-A


V X xx 1 2 x 1 xxxx G

NO of pole	0	Black	RoHS
04 2x2 CONTACTS	3	Orange	Pb<40,000ppm
06 3x2 CONTACTS	5	Green	0000 Standard @ Logo
... ..	6	Blue	000A Standard ANY Logo
48 24x2 CONTACTS	8	Grey	Any special item by customer request, please contact sales department.

Dim.L=(N/2-1)×3.5+10.3
Dim.P=(N/2-1)×3.5
Dim.K=(N/2-1)×3.5

N=Number of poles

POLES	Dim. Tol	Dim.L	Dim.P
2x2p-2x6p		±0.15	±0.10
2x7p-2x12p		±0.25	±0.20
2x13p-2x18p		±0.35	±0.30
2x19p-2x24p		±0.40	±0.35



P.C.B Layout

ANYTEK

INSPECTION COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VX 3.5mm Series With flange Right-angle				DWG NO.	8VX0001	
PART NO.	VXxx12x1xxxxG				CUST NO.		
APPROVED	CHECKED	DESIGNED	DRAWN			Tolerance	
		Runner	Chen Bo			X.	±0.50
		2011.04.25	2011.04.25			X.X	±0.30
						X.XX	±0.10
						X°	±1°