

F

E

D

C

B

A

F

E


D

C

B

A



REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
1	RELEASED PER E050358aLEK	11/23/05	SH
2	REVISED PER E064344GK	05/30/06	REJH
3	REVISED PER E101188KUK	09/24/10	AR



NOTES:  
1. RoHS COMPLIANT, LEAD FREE PER CST-0001 LATEST REVISION.  
2. BUSS #PCD5-125 OR APPROVED REVISION.'

SPECIFICATIONS:
INTERRUPTING AND VOLTAGE RATINGS: 10kA @ 125 VAC, (300-4200)A @ 250 VDC
TIME-CURRENT CHARACTERISTICS: CARRY 100% OF RATING FOR FOUR HOURS MINIMUM. OPEN AT 200% OF RATING IN TEN SECONDS MAXIMUM. (NON-TIME-DELAY).
AGENCY APPROVALS: U.L. RECOGNIZED; FILE E19180 CSA CERTIFIED; FILE 42731, CLASS 1421-01



DRAWN	DATE	 SWD		
P.E.IENI	08/17/05	<b>FUSE 5AMP 125V PCD-5-R</b>		
MATERIAL	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE INCH [MM] TOLERANCES ARE: DECIMALS      ANGLES X.XX [X.X] = ±0.01 [0.25]      ±1° X.XXX [X.XX] = ±0.005 [0.127]	SIZE	CAGE CODE	DWG NO
FINISH		<b>B</b>	<b>67131</b>	<b>30276</b>
	THIRD ANGLE PROJECTION 	SCALE 4: 1		SHEET 1 OF 1
	DO NOT SCALE DRAWING			

87654321

87654321