

## SUMMARY

### # Wires

Low voltage 19



*Image is for illustrative purpose only*

|                  |                                  |
|------------------|----------------------------------|
| Series           | 2P                               |
| Termination type | Female solder                    |
| IP rating        | 50                               |
| AWG wire size    | 30.00 - 22.00                    |
| Cable Ø          | 0.00 - 0.00 mm                   |
| Status           | active                           |
| Matching parts   | <a href="#">CAB.M19.GLA.C52A</a> |

### Download

[Request a quote](#)

[Catalog](#)

## TECHNICAL DETAILS

### Mechanics

|                   |                                                                              |
|-------------------|------------------------------------------------------------------------------|
| Shell Style/Model | CK*: Fixed receptacle with two nuts (back panel mounting)                    |
| Keying            | 3 keys (alpha=0, gamma=60; Plug: male contacts; Receptacle: female contacts) |
| Housing Material  | PSU (Polysulfone), gray                                                      |
| Weight            | 7.02 g                                                                       |

### Performance

|               |                             |
|---------------|-----------------------------|
| Configuration | 2P.M19 : 19 Low V.          |
| Insulator     | L: PEEK for solder contacts |
| Rated Current | 5 Amps                      |

### Specifications


Contact Type: Solder  
Contact Dia.: 0.7 mm (0.027in)  
Bucket Dia.: 0.8 mm (0.031in)  
Test voltage (kV rms) Contact-contact: 1.4  
Air clearance min.: 0.6 mm  
Creepage distance min.: 0.6 mm

### Others

LEMO products and services are provided "as is". LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.

Endurance (Shell): >1000 mating cycles  
Temp (min / max): -50°C / +150°C  
F ret (min): 150 N  
F ret (max): 250 N  
Steam sterilization: 20 times

## DRAWINGS



### Dimensions

|     | N    | a       |
|-----|------|---------|
| mm. | 23.8 | 3.4-4.9 |
| in. | 0,94 | 0,13    |

## RECOMMENDED BY LEMO

### Tools

LEMO products and services are provided “as is”. LEMO makes no warranties or representations with regard to LEMO product & services or use of them, express, implied or statutory, including for accuracy, completeness, or security. The user is fully responsible for his products and applications using LEMO components.