


SLW Series

1.00MM ZIF RIGHT-ANGLE AND STRAIGHT FFC-FPC CONNECTOR

ZIF FFC-FPC Connector series with top and bottom contact type. These through hole connectors feature a height of 4.00mm for Right-Angle and 5.50mm for Straight type, with 4 to 32 contacts. HLW series connectors have a proven track record in automotive, data, industrial, telecommunications, consumer, and medical application equipment.

- Easy to operate and strong FFC/FPC retention makes it vibration-proof
- Ensures high solderability and high durability
- Operating temperature range of -55°C to +85°C



FEATURES

- ZIF (Zero Insertion Force) mechanism
- Easy cable operation
- Design against solder and flux wicking
- High-temperature, dimensional stable thermoplastic housing
- 4 to 32 positions available
- Lead and halogen-free

BENEFITS

- Stress free mating provides high number of mating cycles
- Simple action and strong FFC/FPC retention ensures contact stability
- Ensures high solderability
- Covers general operating temperature range of -55°C to +85°C
- Supports many applications as a general-purpose product
- Meet environmental, healthy and safety requirement

TECHNICAL INFORMATION

MATERIAL

- Housing: LCP, natural color (UL94V-0)
- Contact: Phosphor bronze
- Tab: Brass

MECHANICAL PERFORMANCE

- FFC/FPC Retention Force: 0.49N/contact min.
- Durability: 10 mating cycles

ELECTRICAL PERFORMANCE

- Voltage Rating: 100V A.C./D.C.
- Current Rating: 1.0A A.C./D.C.
- Contact Resistance: 30mΩ max.(initial value)
- Insulation Resistance: 500MΩ min.
- Dielectric Withstanding Voltage: No short or breakdown after 500V A.C., 1mA, 1min.

ENVIRONMENTAL

- Operating Temperature Range: -55°C to +85°C

APPROVALS & CERTIFICATION

- RoHS compliant

SPECIFICATIONS

- Orientation: Right-angle and straight
- Cable Termination: ZIF
- Cable Type: FFC/ FPC
- Board Termination: Through hole (DIP)
- Contact Location: Bottom
- Height: 4.0mm (Right-angle) and 5.5mm (straight)
- Lead-free tin plating

TARGET MARKETS/APPLICATIONS



Car Multimedia
Car Navigation
Dashboard
Lighting



Gaming
LCD & OLED Displays



Base Station
Switches
Controllers
Storage



Controllers
HMI
Vending Machines
PLC
Drives



Ultrasonic
Patient Monitor
MRI
CT
Infusion Pump
Hospital Bed

PART NUMBER SELECTOR

