





DESCRIPTION: M8 FEMALE - CABLE MOUNT - SOLDER CUP - 6 POS.



NUT



NOTE:

MATERIAL

HOUSING:
CONTACT:
NUT:
GROUND:
O-RING:

PBT UL94V-0, BLACK
BRASS
BRASS
BRASS
NBR, BLACK

FINISH

CONTACT:

GOLD PLATED
OVER 50u" NICKEL
NICKEL PLATED
BRIGHT TIN (60u")

NUT:
GROUND:

ELECTRICAL

RATED CURRENT:
RATED VOLTAGE:
INSULATION RESISTANCE:
CONTACT RESISTANCE:
WATER PROOF:

1.5A
30V
100 MOhms MIN.
10 mOhms MAX.
IP67


ENVIRONMENT

OPERATION TEMPERATURE:
MAX WIRE AWG:

-40°C TO +85°C
24

854-006-203RLSY

1 = GOLD FLASH
4 = 10u" GOLD



RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:

NTS

SHEET

OF

1

1

REV

7

DWG NO.

854-006-203RLSY