




THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


MAY ,21

© COPYRIGHT 02

By -


ALL RIGHTS RESERVED.

LOC J	DIST	REVISIONS 变更					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			—	SEE SHEET 1	—	—	—




- 注記
- 一般公差 : ± 0.2
 - 適用ピン リセプタクル型番 : □ -170063-□ , □ -353937-□ , □ -1123655-□
 - 適用規格番号: 108-5205(型番171370-3)
108-61239(型番171370-4)
108-5541(型番171370-5)
- △4 PARTS COMPLY WITH GLOW WIRE 750 PER IEC 60335-1.
△5 MUST BE APPLIED ON THE OUTSIDE OF COMPRESSOR.

- NOTES;
- GENERAL TOLERANCE ± 0.2
 - APPLICABLE CONTACT PART No.:
□ -170063-□ , □ -353937-□ , □ -1123655-□
 - PRODUCT SPEC No.: 108-5205(FOR PART No.171370-3)
108-61239(FOR PART No.171370-4)
108-5541(FOR PART No.171370-5)
- △4 GLOW WIRE 750(IEC 60335-1), CTI 600V(HALOGEN FREE)
△5 MUST BE APPLIED ON THE OUTSIDE OF COMPRESSOR.




断面 "A" - "A"
SECT






断面 "B" - "B"
SECT

171370-5	PBT ガラス強化 PBT GLASS FILLED(UL94V-0)	灰色 (GRAY)
171370-4	PBT ガラス強化 PBT GLASS FILLED(UL94V-0)	黒 (BLACK)
171370-3	PBT ガラス強化 PBT GLASS FILLED(UL94HB)	自然色 (NATURAL)
型番 (PART No.)	材料 (MATERIAL)	色 (COLOR)



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity			
DIMENSIONS: 単位: 耗 mm		CHK				
		APVD	NAME 名称			
		PRODUCT SPEC 製品規格	2.3 DIA CLUSTER BLOCK			
MATERIAL 材料		APPLICATION SPEC 取付適用規格	Φ2.3 クラスタブロック			
		WEIGHT	SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED TO
SEE TABLE		CUSTOMER DRAWING	A3	00779	C-171370	-
			SCALE 尺度	4:1	SHEET 2 of 3	REV R1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
J			—	SEE SHEET 1	—	—	—



断面“B”-“B”
SECT


注記、

1. 一般公差 : ± 0.2
2. 適用ピン リセプタクル型番 : □ -170063-□, □ -353937-□, □ -1123655-□
3. 適用規格番号: 108-140004 (型番171370-7)
4. PRELIMINARY-NOT FOR PRODUCTION
5. PARTS COMPLY WITH GLOW WIRE REQUIREMENTS
DETAILED IN IEC 60335-1

NOTES;

1. GENERAL TOLERANCE ± 0.2
2. APPLICABLE CONTACT PART No. :
□ -170063-□ , □ -353937-□ , □ -1123655-□
3. PRODUCT SPEC No.: 108-140004 (FOR PART No. 171370-7)
4. PRELIMINARY-NOT FOR PRODUCTION
5. PARTS COMPLY WITH GLOW WIRE REQUIREMENTS
DETAILED IN IEC 60335-1
6. PRELIMINARY PART

△ ₆	171370-8	PPS (UL94V-0)	(NATURAL)
△ ₅	171370-6	PA 6 GLASS FILLED	自然色 (NATURAL)
	171370-7	液晶ポリマー (UL94V-0) LCP (UL94V-0)	自然色 (NATURAL)
	型 番 (PART No.)	材 料 (MATERIAL)	色 (COLOR)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN		 TE Connectivity			
		CHK					
DIMENSIONS: 単位： 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		NAME 名称			
		0 PLC ±		2.3 DIA CLUSTER BLOCK			
		1 PLC ±		Φ 2.3 クラスタブロック			
		2 PLC ±		SIZE A3			
		3 PLC ±					
		4 PLC ±		CAGE CODE 00779			
		ANGLES ±		DRAWING NO 番号 C-171370			
MATERIAL 材料		FINISH 仕上		RESTRICTED TO —			
SEE TABLE		WEIGHT					
		CUSTOMER DRAWING		SCALE 尺度 4:1			
				SHEET 3 OF 3			
				REV R1			