

D10100DB/17

A

B


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE		COLOR (DIN)	WIRE STRIP LENGTH +1/32 -0 [+0,8 -0]	WIRE CLASS	DIMENSIONS in. [mm]				MAX WIRE INSUL DIA	INSTALLATION TOOLS/DIES	
	AWG	[mm²]				L	P	ID	OD (REF.)		MANUAL	PNEUMATIC
* FSDX75-8	22-20	[0,50]	WHITE	15/32 [11,91]	B, K, M	0.53 [13,5]	0.31 [8,0]	0.04 [1,1]	0.05 [1,4]	0.12 [3,0]	CT-1002 CT-1003 CT-1090 ^CD-090 CT-1123 CT-1160 CT-1170 #CT-2523CH	CTFP-25 CTFP-40
FSDX76-8	18	[0,75]	GRAY	15/32 [11,9]	B, K, M	0.55 [14,0]	0.31 [8,0]	0.05 [1,3]	0.06 [1,6]	0.14 [3,4]		
FSDX77-8	-	[1,0]	RED	15/32 [11,9]	B, K, M	0.57 [14,5]	0.31 [8,0]	0.06 [1,5]	0.07 [1,8]	0.14 [3,4]		
FSDX78-8	16	[1,5]	BLACK	15/32 [11,9]	B, K, M	0.57 [14,5]	0.31 [8,0]	0.07 [1,8]	0.08 [2,1]	0.15 [3,8]		
FSDX78-10				17/32 [13,5]	B, K, M	0.63 [16,0]	0.39 [10,0]					
FSDX80-8	14	[2,5]	BLUE	15/32 [11,9]	B, K, M	0.63 [16,0]	0.31 [8,0]	0.09 [2,3]	0.10 [2,6]	0.19 [4,8]		
FSDX80-12				5/8 [15,9]	B, K, M	0.79 [20,0]	0.47 [12,0]					
FSDX81-10	12	[4,0]	GRAY	17/32 [13,5]	G, K, M	0.71 [18,0]	0.39 [10,0]	0.11 [2,9]	0.13 [3,3]	0.24 [6,2]		CTFP-40 CTFP-100
FSDX81-12				5/8 [15,9]	G, K, M	0.79 [20,0]	0.47 [12,0]					
FSDX84-12	6	[16,0]	BLUE	5/8 [15,9]	G, H, I, K, M	.91 [23,0]	0.47 [12,0]	0.24 [6,0]	0.25 [6,4]	0.37 [9,5]	+CT-1004 CT-1104 #CT-2504CH	---

* UL LISTED WITH 20 AWG ONLY, UL486F SCOPE IS 20 - 1/0 AWG. WHITE IS DIN COLOR FOR 20 AWG [0,5]
+ TOOL/PART IS NOT A UL LISTED COMBINATION
^ DIES USED WITH CT-2300 TOOL
CRIMP HEAD USED WITH CT-2500 TOOL

NOTES:


1. USED FOR:
A. UL LISTED WITH STRANDED COPPER WIRE ONLY
B. 221°F [105°C] MAX. OPERATING TEMPERATURE
2. MATERIAL:
A. STAMPING: COPPER, TIN PLATED
B. HOUSING: POLYPROPYLENE, COLOR CODED
C. COLOR CODE CONFORMS TO DIN STANDARD
3. SEE www.panduit.com FOR PACKAGE QUANTITIES
4. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



LISTED
E472545



CERTIFIED
LR31212

TITLE				
FERRULES WITH SLEEVES SINGLE WIRE DIN END SLEEVES FSDX: LARGER SLEEVE DIAMETER CUSTOMER/AGENCY DRAWING				
ITEM REVISION NAME				
N41752BA/09				
DATASET FILE NAME				
N41752BA_DC/09				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 ° 			MATERIAL: SEE NOTES	
			DRAWING NUMBER: A41752	
DRAWN BY	DATE	CHK	SCALE	SIZE
FCHE	8/31/2018		N.T.S.	SHT 1 OF 1 B

A

B



2

1