




N=NUMBER OF POLES

Dim L	N×5.0+1.00
Dim B	(N-1)×5.0

POLES	Dim L	Dim B
1p	±0.1	
2p-6p	±0.2	±0.15
7p-12p	±0.3	±0.25
13p-18p	±0.4	±0.35
19p-24p	±0.45	±0.4

SIGN	DATE	DESCRIPTION	APPROVER
△	01/24/07	The Soldering temperature from 245° to 250°	Aaron
△	01/24/07	Add "VDE" stipulation	Aaron
△	05/19/09	wire strip length changed from 6-7mm to 9-10mm	Eris
△	05/19/09	temperature changed from -30°C-105°C to -40°C-115°C	Eris
△	05/19/09	The tolerance of dimension is changed	Eris
△	01/11/11	The view is changed	Runner
△	01/02/13	change the electrical specification and the dimension from 3.6 to 3.3	Da cheng

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!



P.C.B. LAYOUT
△ Top view

△ Material

- Item ① Terminal housing: Thermoplastic (UL94V-0)
- Item ② Solder Pin: Brass Tin plated.
- Item ③ Lever : Thermoplastic (UL94V-0) Natural color
- Item ④ Spring clamp : Stainless steel
- Item ⑤ Terminal Cover : Thermoplastic (UL94V-0)

△ Electrical

- Voltage rating: 300VAC 450VAC
- Current rating: 10A 6A
- Wire range: 0.5mm²
- Solid wire(AWG): 14-20
- Stranded wire(AWG): 14-20
- Wire strip length: 9-10mm
- Withstanding Voltage: 1.6KV 2.5KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension:

HBxx01x0xxxxG

- No. OF POLES
01: 1 POLES
02: 2 POLES
:
:
24: 24 POLES
- △ Body Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7004/P)
9 White(RAL1102)
C Multiple colors
- 0000 Standard @ Logo
000A Standard ANY Logo
Any special item by customer request, please contact sales department.
- △ RoHs compliant (lead<4%) In copper Alloy

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HB - 5.0mm Series (Single wire)			
PART NO.	HBxx01x0xxxxG		DWG NO.	8HB0001	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Da cheng 2013.01.02	Da cheng 2013.01.02		UNIT: mm SCALE: NONE REV: G
				SHEET: 01/01	X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°