





NOTE:

- MATERIAL, HOUSING: NYLON 6T (E630NK), UL94V-0
TERMINAL: C2700 H
- FINISH: GOLD AT CONTACT, G/F OVER 1um(40u") MIN Ni OVER ALL
- SPEC.:
PRODUCT SPEC: GS-12-629
PACKING SPEC: GS-14-1517
- THE HSG. WILL WITHSTAND EXPOSURE TO 260C PEAK TEMP. FOR 10 SEC. IN A CONVECTION, INFRA-RED OR VAPOR PHASE REFLOW OVEN.
- MATING SIDE LENGTH: 2.50MM MIN.
- PRODUCT NUMBERING:
200218 3 3 - XXX XX X X LF

LEAD FREE
PLATING:
1: G/F ALL OVER
4: 0.25um(10U") GOLD AT CONTACT
8: 0.76um(30U") GOLD AT CONTACT
PACKING
T: TUBE
PIN COUNT
04, 06, 08, ..., 48, 50
(EVERY EVEN PIN)
STACK HEIGHT "K"
EXAMPLE: 045=4.5MM
IN 0.5MM INCREMENT



Recommended P.C.B. Layout
Layout Tolerance = ± 0.05 mm

mat'l. code				tolerances unless otherwise specified		CUSTOMER COPY	 www.fciconnect.com		
ltr	ecn no	dr	date	linear	.X ± 0.38				
A	T10-0088	S.LIN	10'-7-15	linear	.XX ± 0.25	projection	title 1.27X1.27MM BTB STACK HD VT, SMT		
				angles	.XXX ± 0.15				
					0° ± 2°				
				dr	STERLING LIN	10'-7-15	MM	product family 585	
				enrg	STERLING LIN	10'-7-15		size dwg no	
				chr	STERLING LIN	10'-7-15	scale	A4	
				appd	GARY HSIEH	10'-7-15		20021833	
sheet index	revision sheet	A	1						