





2P mark



POLE		2	3	4	5	6	7	8	9	10	11	12
A		5.60	8.10	10.60	13.10	15.60	18.10	20.60	23.10	25.60	28.10	30.60
B		2.50	5.00	7.50	10.00	12.50	15.00	17.50	20.00	22.50	25.00	27.50
Tol.		±0.10					±0.15					
POLE	13	14	15	16	17	18	19	20	21	22	23	24
A	33.10	35.60	38.10	40.60	43.10	45.60	48.10	50.60	53.10	55.60	58.10	60.60
B	30.00	32.50	35.00	37.50	40.00	42.50	45.00	47.50	50.00	52.50	55.00	57.50
Tol.		±0.20						±0.30				

SIGN	DATE	DESCRIPTION	APPROVER
△	2009.5.13	The design is changed	Jacke
△	2009.5.13	The voltage rating and withstanding Voltage are changed	Jacke
△	2009.5.13	The Operating temperature is changed	Jacke
△	2009.5.13	Add UL standard	Jacke
△	11/21'09	The normal grey No. changed from RAL7004/P to RAL7035/D	Kind
△	03/17'10	Add the 2P mark	RUNNER
△	05/22'10	Structure changed	RUNNER
△	09/01'10	The design is changed	RUNNER

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ① Insulator(lever): Thermoplastic (UL94V-0)
- Item ② Down Insulator(housing): Thermoplastic (UL94V-0)
- Item ③ Wire guard: Stainless steel
- Item ④ Terminal Body(contact pin): PhBz.Tin plated
- Item ⑤ Up Insulator(housing): Thermoplastic (UL94V-0)

Electrical: cULus

- △ ● Voltage rating: 150V
- Current rating: 4A
- Wire range:
 - Solid wire(AWG): 20-28
 - Stranded wire(AWG): 20-28
- △ ● Wire strip length: 7-8mm
- △ ● Withstanding Voltage: 1.3KV
- △ ● Operating temperature: -40°C to +115°C
- △ ● Safety Approval:

HW xx B 0 x 0 xxxx G

No. OF POLES

02: 2 POLES

⋮

24: 24 POLES

COLOR

0: BLACK

5: GREEN (RAL 6018/T)

6: BLUE

△ 8: GREY (RAL 7035/D)

G: Pb<40000ppm

0000: "@" Logo (Standard)

000A: "ANYTEK" Mark

Any special item by
customer request.
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		HW 2.5mm Series			
PART NO.	HWxxB0x0xxxxG			DWG NO.	8HW0301
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance
		Runner 2010.09.01	Jacke 2009.06.04		UNIT: mm SCALE: NONE SHEET: 01/01 REV.: G
					X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°