



NOTES:


1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS ASSEMBLED INTO CONNECTOR.
3. BACK WELL FILLED WITH EPOXY.
4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.
5. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.114in [W4281-1XPG-3ES]
 - INTERMEDIATE = 0.202in [W4291-1XPG-3ES]
 - LONG = 0.257in [W4292-1XPG-3ES]





FACE VIEW
W4281-10PG-3ES
10-POS.




FACE VIEW
W4281-11PG-3ES
11-POS.



FACE VIEW
W4281-12PG-3ES
12-POS.




PC TAIL LAYOUT



HEX NUT
MAT'L: UV THERMOPLASTIC,
BLACK


O-RING
MAT'L: RUBBER,
BLACK

13/16-27 UNS-2A
MOD. THREAD




PANEL INSERT, PIN
MAT'L: UV THERMOPLASTIC,
BLACK

PIN CONTACT
PC TAIL, SHORT
GOLD PLATED



PC TAIL VIEW
W4281-10PG-3ES - 10-POS. (11&12 CLOSED)
W4281-11PG-3ES - 11-POS. (12 CLOSED)
W4281-12PG-3ES - 12-POS. (ALL OPEN)



**RECOMMENDED
PANEL CUTOUT**
STANDARD MULTI-CON-X

ASS'Y P/N	CONTACTS	HOLE POS. CLOSED
W4281-10PG-3ES	10 - #20	11, 12
W4281-11PG-3ES	11 - #20	12
W4281-12PG-3ES	12 - #20	NONE
W4281-1XPG-3ES		

NO. OF CONTACTS

CUSTOMER APPROVAL

THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.

APPROVED BY: _____

DATE: _____

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1		
REV.	INIT.	DATE	DESCRIPTION		
	PAK	10/02/14	ORIG. DRAWN BY:	DATE:	 601 E. WILDWOOD VILLA PARK, IL 60181
ALL INFORMATION ILLUSTRATED IS THE PROPERTY OF "CONXALL CORPORATION". UNAUTHORIZED DUPLICATION OR DISTRIBUTION OF THIS DOCUMENT IS PROHIBITED.			CHECKED BY:		
ALL UNITS ARE IN FEET, INCHES, FRACTION OF INCHES AND DECIMALS.			APPROVED BY:		TITLE: PANEL PIN, W/ EPOXY 12-POS., #20 PC TAIL, SHORT (STD.) MULTI-CON-X, E-KEY, WEATHER RESISTANT CUSTOMER: STANDARD PRODUCT
UNLESS OTHERWISE SPECIFIED TOLERANCES 3 PLACE DECIMALS ±.005 ANGLES ±1° FRACTIONS ±1/16			SCALE NTS	SIZE B	
FILE: W4281-1XPG-3ES			DIRECTORY: SLW	SHEET 1 OF 1	PART NUMBER: W4281-1XPG-3ES
C = CRITICAL CHARACTERISTIC FLAG PER SPEC. XXXX					REV A