

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20


© COPYRIGHT 20

BY -

ALL RIGHTS RESERVED.




REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	C2	REVISED PER ECO-14-015436	13OCT2014	NK	MM




WIRE ENTRY

MATING FACE



POLARIZATION KEY SLOT

CLAMPING SCREW




284507-3 AS SHOWN

- 1 MATERIALS AND FINISH
HOUSING: PA 6.6, UL 94-V0, COLOR GREEN
CLAMP: BRASS, NICKEL PLATED
TERMINAL: BRASS, TIN PLATED
CONTACT SPRING: PHOSPHOR BRONZE, TIN PLATED
CLAMPING SCREW: M2, BRASS, NICKEL PLATED
- 2 END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING
- 3 WIRE SIZE RANGE
14 - 30 AWG
- 4 NOT CUMULATIVE TOLERANCE
- 5 HOUSING: PA 6.6, UL 94-V0, COLOR: RED
- 6 PRELIMINARY - NOT RELEASED FOR PRODUCTION

6	5	19.05	5	3-284507-5
		10.5	4	3-284507-4
		7.0	3	3-284507-3
		95.25	25	2-284507-5
		91.44	24	2-284507-4
		87.63	23	2-284507-3
		83.82	22	2-284507-2
		80.01	21	2-284507-1
		76.20	20	2-284507-0
		72.39	19	1-284507-9
		68.58	18	1-284507-8
		64.77	17	1-284507-7
		60.96	16	1-284507-6
		57.15	15	1-284507-5
		53.34	14	1-284507-4
		49.53	13	1-284507-3
		45.72	12	1-284507-2
		41.91	11	1-284507-1
		38.10	10	1-284507-0
		34.29	9	284507-9
		30.48	8	284507-8
		26.67	7	284507-7
		22.86	6	284507-6
		19.05	5	284507-5
		15.24	4	284507-4
		11.43	3	284507-3
		7.62	2	284507-2
		DIM A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm



MATERIAL

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±
1 PLC ±0.30
2 PLC ±0.25
3 PLC ±
4 PLC ±
ANGLES ±2°

FINISH

DWN 05FEB2002

E. ZANOLINI

CHK 05FEB2002

E. ZANOLINI

APVD 05FEB2002

D. BIEVENOUR

PRODUCT SPEC

108-20166

APPLICATION SPEC

114-20079

WEIGHT

-

CUSTOMER DRAWING



TE Connectivity

NAME

TERMINAL BLOCK PLUG
STACKING
3.81mm PITCH

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-284507

-

SCALE

4:1

SHEET

OF

REV

C2