


3M

Scotchlok™ Terminals

M8BC, M6BC, M4BC

Butt Connector, Non-Insulated, Brazed Seam



Data Sheet

Product Number	Wire Range (AWG)	L	Thickness	Barrel Length	Barrel I.D.
M8BC	8	0.81	0.050	0.38	0.175
M6BC	6	1.02	0.050	0.47	0.250
M4BC	4	1.13	0.075	0.53	0.280



UNDERWRITERS
LABORATORIES
STANDARD NO. UL 486C
3M FILE NO. E23438



CANADIAN STANDARDS
ASSOCIATION
STANDARD NO. 22.2
NO. 0, 65
3M FILE NO. LR22190

Installation Information

WARNING

Turn power off before installing or removing terminal. All electrical work should be done according to appropriate electrical codes.

UL Listed and CSA Certified for use on stranded copper (AWG) wire only.

Strip away the end of wire insulation; 1/2 inch for 8 AWG, 9/16 inch for 6 AWG and 5/8 inch for 4 AWG.

Make the crimp in the proper station of a recommended 3M crimp tool: 3M TH-450 (for 8 and 6 AWG); (T & B) WT-115A, Burndy MY29-3.



 Barrel Crimp (Required)

Specifications

Wire Size:
Barrel Seam:
Maximum Current:
Terminal Material:
Terminal Plating:

See Table Above
Braze
Same as Wire
ETP Copper
Tin

Engineering Specification

Crimp-type connectors shall, electrically and mechanically, connect permanently to the pre-stripped ends of two stranded copper wires.

The connector line shall offer barrel variations in wire (AWG) size (8, 6, 4) and construction (non-insulated brazed seam, vinyl insulated butted seam, nylon insulated seamless, etc...). The connector line shall have regulatory agency coverage (UL Listing, CSA Certification). The connectors shall be marked with the wire range and manufacturer's symbol (↑).

The non-insulated, brazed seam butt connector shall be tin-plated, annealed copper, having a double-length, round brazed seam barrel, with a center stop, sized for a specified (AWG) wire range (8, 6, 4).

3M and Scotchlok are trademarks of 3M.



is a trademark of Underwriters Laboratories.



is a trademark of Canadian Standards Association.

IMPORTANT NOTICE

Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

Warranty; Limited Remedy; Limited Liability. This product will be free from defects in material and manufacture as of the date of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any loss or damage arising from this 3M product, whether direct, indirect, special, incidental or consequential regardless of the legal theory asserted.**



Electrical Products Division

6801 River Place Blvd.
Austin, TX 78726-9000
<http://www.3M.com/elpd>

Litho in USA.
© 3M 2002 78-8125-9665-4-A