

IE-PS-V04P-2SC-MM-BP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

PushPull plug-in connector set according to IEC
61076-3-106 ver.4 (IEC24702), plastic with SC insert

General ordering data

Version	FO connector, Variant 4, SC-Duplex multi-mode, with kink prevention, IP67
Order No.	1963370000
Type	IE-PS-V04P-2SC-MM-BP
GTIN (EAN)	4032248651849
Qty.	10 pc(s).

Creation date September 17, 2022 8:16:53 PM CEST

Catalogue status 09.09.2022 / We reserve the right to make technical changes.

IE-PS-V04P-2SC-MM-BP**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Depth	129.8 mm	Depth (inches)	5.11 inch
Height	20.1 mm	Height (inches)	0.791 inch
Width	20.2 mm	Width (inches)	0.795 inch
Net weight	3.4 g		

Temperatures

Operating temperature -40 °C...70 °C

Environmental Product Compliance

REACH SVHC	Lead 7439-92-1, 6,6'-di-tert-butyl-2,2'-methylenedi-p-cresol 119-47-1	SCIP	e5bbf197-73b5-420b-90c0-0173b7b
------------	---	------	---------------------------------

General data

Colour	Miscellaneous	Connection 1	SCRJ
Connection 2	gluing, crimping, polishing	Description of article	Variant 4, SC-Duplex multimode, with kink prevention
Fibre type	Multimode	Housing main material	PA UL 94 V0
Housing material, insert	PA, Zinc diecast	Insertion loss	0.5 dB singlemode; 0.4 dB multimode; 1.5 dB POF
Plugging cycles	500	Protection degree	IP67
Return loss (attenuation)	40 dB singlemode; 30 dB multimode	Sheath diameter, max.	10 mm
Sheath diameter, min.	5 mm		

General standards

Connector standard	IEC 61076-3-106 Var. 4, IEC 61754-24
--------------------	--------------------------------------

Classifications

ETIM 6.0	EC001122	ETIM 7.0	EC001122
ETIM 8.0	EC001122	ECLASS 9.0	19-17-01-22
ECLASS 9.1	19-17-01-22	ECLASS 10.0	19-17-01-22
ECLASS 11.0	19-17-01-22	ECLASS 12.0	19-17-01-22

Approvals

Approvals



ROHS

Conform

IE-PS-V04P-2SC-MM-BP

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data

Downloads

Approval/Certificate/Document of
Conformity

[GOST Approval](#)

Engineering Data

[WSCAD](#)

Product Change Notification

[20210412 Technical change for cap nut V1 and V4](#)

[20210412 Technische Änderung zu Hutmutter V1 und V4](#)

User Documentation

[MAN IE GUIDE DE](#)

[MAN IE GUIDE EN](#)

[Designation key / Type key](#)

Catalogues

[Catalogues in PDF-format](#)

Brochures

[FL FIELDWIRING EN](#)

[PI PROFINET CABLING EN](#)

[PI PROFINET CABLING EN](#)

IE-PS-V04P-2SC-MM-BP

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Dimensioned drawing

