



THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.




REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190346	2019/03/05	Vicky	Change Note




Recommended Panel
Cut-Out




With Liquid Glue



8 Pin




7 Pin




6 Pin


Pin Assignments Front View




5 Pin



4 Pin




3 Pin



2 Pin


Pin Assignments Front View



ABD-XXRMMS-LC7001

02:2Pin

08:8Pin



- Note:
- * Important Dimension.
 - * Waterproof Rate: IP67, Unmated.
 - * Housing: Thermoplastic, Black.
 - * Pin: Copper Alloy, Gold Plated.
 - * Nut: Thermoplastic, Black.
 - * Gasket: Rubber, Gray.
 - * Panel Thickness Max: 3.5mm
 - * Gasket and Nut are packed separately in PE bags. (Gasket/Nut不組裝，散裝出貨)

UNIT:mm		TOLERANCE		TITLE	
.X	±0.25	STANDARD		PANEL LOCK M CONN M PIN	
.XX	±0.1	SCALE	3:2	SIZE	A4
.XXX	±0.05	REV.	B	WC-REV.	A.1
ANGLES	±1°	SHEET		1 OF 1	
		QC		Inspection item	

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
DWG NO	Vicky	2019-03-05
CUSTOMER	ABD-XXRMMS-LC7001	CHECKED BY
ALTW	Rita	DATE
	Max	2019-03-05
		APPROVED BY
		DATE
		2019-03-05