





THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN BSV		04N2V04		 TE Connectivity	
		CHK J OLSON		--			
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME		AMPMODU MOD II RECEPTACLE ASSEMBLY, HORIZONTAL, 100 CL, 2 ROW, CLOSED-ENTRY, SHORT POINT OF CONTACT, END-TO-END STACKABLE	
mm		0 P/LC ± -- 1 P/LC ± -- 2 P/LC ± 0.1% [.005] 3 P/LC ± -- 4 P/LC ± -- ANGLES ± --					
				PRODUCT SPEC			
				108-25026			
				APPLICATION SPEC			
				114-25018			
MATERIAL		FINISH		WEIGHT		RESTRICTED TO	
				--		A1 00779 C5535512 --	
CUSTOMER DRAWING				SCALE		SHEET 1 OF 1 REV B	