





APPROVED: _____
DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	5/25/05	
A		REDRAWN	10/30/13	AY/NP



SPECIFICATIONS:

Material: Insulator: Hi-temp thermoplastic, rated UL 94V-0
Insulator color: Black
Contacts: Phosphor Bronze
Plating: Gold flash over Nickel underplate overall
Electrical: Current rating: 1 Amp max.
Contact resistance: 20 mohms max. initial
Insulation resistance: 1,000 Mohms min.
Dielectric withstanding voltage: 500 VAC for 1 minute
Temperature Rating: Operating temperature: -40°C to +105°C
Environmental: Lead free, RoHS compliant

Positions: 02 thru 50
A = .050 [1.27] x No. of Positions + .016 [0.40]
B = .050 [1.27] x No. of Spaces

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS ARE INCHES [MM] TOLERANCES: EXCEPT AS NOTED INCHES				ADAM TECH 909 Rahway Avenue, Union, NJ 07083 Phone: 908-687-5000 Fax: 908-687-5710			
HOLES				TITLE .050 [1.27] SINGLE ROW RECEPTACLE STRIP LOW PROFILE, GOLD PLATED			
.X	± .10	Ø.X	± .10				
.XX	± .020	Ø.XX	± .015				
.XXX	± .015	Ø.XXX	± .010				
APPROVALS				DATE			
DRAWN	SS	5/25/05		SIZE X PART NO. HRS-1B-XX-GA REV. A			
CHECKED							
APPROVED							
REF: S00019C				SCALE: NTS			
				SHEET 1 OF 1			