

AX102250 Faceplates and Panels - KeyConnect Faceplates 6-Port w/ID Windows Single-Gang



For more Information
please call

1-800-Belden1

**General Description:**

KeyConnect Faceplates 6-Port, w/ ID Windows, Single Gang, Flush

Usage (Overall)

Suitable Applications:	- Compatible with a variety of modules that are suitable for use with Belden IBDN Systems 10GX, 4800, 3600, 2400, 1200, fiber and coax.
Related Parts:	- Compatible with REVConnect Jacks (UTP & STP), KeyConnect Jacks (UTP) and Keyconnect Multimedia Modules. See notes if using KeyConnect Shielded (STP) Jacks.

Physical Characteristics (Connectivity)**Capacity**

Max. Capacity:	6-port
-----------------------	--------

Access

Front Connection:	Flush
--------------------------	-------

Dimensions**Dimensions:**

Height (mm)	Width (mm)	Depth (mm)
114.300	69.850	6.604

Materials**Materials:**

Description	Material
Plate	Plastic - UL94V-0

Color

Color:	Almond
---------------	--------

Weight

Weight:	0.027 kg
----------------	----------

Included Parts

Included Parts:	6-32 screws, carton labels, clear windows, KeyConnect blank inserts.
------------------------	--

Packaging

Packaging:	Individually packaged in a plastic bag.
-------------------	---

Mechanical Characteristics (Connectivity)

Connector/Hardware Retention:	88.964 N
Storage Temperature Range:	-40°C To +70°C
Installation Temperature Range:	-10°C To +60°C
Operating Temperature Range:	-10°C To +60°C

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	07/01/2006

METRIC MEASUREMENT VERSION

AX102250 Faceplates and Panels - KeyConnect Faceplates 6-Port w/ID Windows Single-Gang

MII Order #39 (China RoHS):	Yes
Safety Listing:	c(UL)us Listed

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Transmission Characteristics (Connectivity)**Notes (Overall)**

Notes: Please contact Tech Support if using Shielded KeyConnect jacks (AX104562, AX104595, AX104596) for compatibility verification.

Product Family**Part Numbers:**

Item Number	Stainless Steel	Dark Gray	Almond	Black	Ivory	Elec. White	Gray
1-Port w/ ID Windows Single-gang	AX104230	-	AX103922	AX104160	AX104565	AX102660	AX107021
2-Port w/ ID Windows Single-gang	AX104231	AX104455	AX103923	AX104161	AX104197	AX102655	AX107022
3-Port w/ ID Windows Single-gang	-	-	AX103924	AX104162	-	AX102661	-
4-Port w/ ID Windows Single-gang	AX104232	AX104464	AX102248	AX104163	AX104198	AX102249	AX107023
6-Port w/ ID Windows Single-gang	AX104233	-	AX102250	AX104164	AX104199	AX102251	AX107024
4-Port w/ ID Windows Double-gang	AX104479	-	-	-	-	-	-
6-Port w/ ID Windows Double-gang	AX104480	AX106594	AX102670	AX104165	AX104566	AX102671	AX107025
12-Port w/ ID Windows Double-gang	AX104234	-	AX102256	AX104166	AX104200	AX102257	-
1-Port Single-gang	AX102006	-	-	-	-	-	-
2-Port Single-gang	AX102007	-	-	-	-	-	-
4-Port Single-gang	AX102009	-	-	-	-	-	-
6-Port Single-gang	AX102010	-	-	-	-	-	-
6-Port Double-gang	AX102012	-	-	-	-	-	-
12-Port Double-gang	AX102013	-	-	-	-	-	-
Wall Mount Phone Plate	AX104126	-	-	-	-	AX102902	-
Single-gang Back Box 1.89 in.	-	-	AX104127	-	-	AX102657	-
Double-gang Back Box 1.89 in.	-	-	AX104130	AX106684	-	AX104131	AX106685

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
AX102250	1 EA	0.030 KG			KCONN FACEPLATE 6-P SG ALMOND

Revision Number: 1 Revision Date: 08-16-2017

© 2019 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.