





	Dim A	Dim B
2-6p	± 0.15	± 0.15
7-12p	± 0.25	± 0.25
13-18p	± 0.30	± 0.30
19-24p	± 0.40	± 0.40

02	2 CONTACTS
03	3 CONTACTS
...	...
24	24 CONTACTS

Color	0000: "@ " Logo
Black (RAL9005)	000A: "ANYTEK" Mark
Red (RAL3001/D)	0091: "ANYTEK" Mark
Orange(RAL2011/P)	Any special item by
Yellow(RAL1018/A)	customer request.
Green(RAL6018/T)	please contact sales
Blue (RAL 5015/A)	department.

ANYTEK				CUSTOMER COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATSOEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE		TS-5.0mm Series(W/latching hooks on the back side) With flange					
PART NO.		TSxx71xDxxxxG		DWG NO.		8TS0004 	
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
				Chen Bo 2010.08.16	 		X. ±0.50 X.X ±0.30 X.XX ±0.10 X° ±1°
					UNIT: mm SCALE: NONE SHEET: 01/01 REV: I		