

# CT2060

## Banana Plug Test Lead, PVC

4mm Straight Banana Plug to Straight Banana Plug Test Lead

### Description

4mm banana plugs on both ends. With 18 AWG (0.75 mm<sup>2</sup>)

PVC jacketed lead wire.



*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

# Datasheet

All specifications apply to the unit after a temperature stabilization time of 20 minutes over an ambient temperature range of 25°C ± 5°C.

### Specifications

<b>IEC Rating</b>	33 V AC / 70 V DC
<b>Voltage, Max</b>	1,200 V AC/DC
<b>Current, Max</b>	12 A
<b>Jacket Material</b>	PVC
<b>Conductor Area</b>	0.75 mm <sup>2</sup>
<b>Wire Gauge</b>	18 AWG
<b>Stranding (# x dia.)</b>	195 x 0.07 mm
<b>OD</b>	3.7 mm (0.146")
<b>Temperature (degrees)</b>	-20 to +80C
<b>RoHS (2011/65/EU)</b>	Compliant

Specifications are subject to change without notice. To ensure the most current version of this manual, please download the current version from our website: [caltestelectronics.com](http://caltestelectronics.com)

*Technical data subject to change.*

© Cal Test Electronics 2018.

[caltestelectronics.com](http://caltestelectronics.com)

