


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART#	DESCRIPTION	WEIGHT*
CJSK688TG**	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)



*WEIGHT IS APPROXIMATE
** = JACK COLOR/KEY SUFFIX
(SEE SHEET 2)



NOTES:


1. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
2. MATERIAL:
MODULE HOUSING-ABS
NOMINAL WALL THICKNESS .078(2.0).
WIRE CAP-PC/ZINC
3. ALL MINI-COM TX6 PLUS 8 POSITION, 8 WIRE, KEYED JACK MODULES ARE NOT UNIVERSAL IN DESIGN. EACH MODULE ACCEPTS ONLY ONE SPECIFIC KEYED PLUG THAT MATCHES THE JACK KEYED CONFIGURATION.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.

KEYED FEATURE
(SEE SHEET 2)




ACTUAL SIZE

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	6-21-10	MDJr	SK	B. ADDED JACK MODULES FOR VIOLET AND INTERNATIONAL GRAY KEYS.	03011-58		480		
1	1-27-09	MDJr	PBD	A. UPDATED JACK MODELS ON SHEET 2.	03011-58		VMB		
R	12-01-08	MDJr	BMBA	RELEASED TO PRODUCTION	03011-58		VMB		

MODEL FILENAME M03011AA/01		SIZE A
DRAWING FILENAME M03011E1_DC58/01C		
TITLE MINI-COM TX6 PLUS SHIELDED KEYED JACK MODULE CUSTOMER DRAWING		
 PANDUIT TM CORP. TINLEY PARK, ILL 60477	I.I. NUMBER	PRODUCT SPEC
	WORK INSTRUCTION	
 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±	SCALE FULL
DRAWN BY MDJr	REVIEW DRAWING NUMBERS	PART NO. CJSK688TG**
DATE 10-22-08		DRAWING NO. 03011-58 SHEET 1 OF 2
CHK'D BMBA		


△ SHIELDED JACK COLOR/KEY CODE AND PART NUMBER

A - BLACK




CJSK688TGBL

B - RED




CJSK688TGRD

C - GREEN




CJSK688TGGR

D - YELLOW




CJSK688TGYL

E - ORANGE




CJSK688TGOR

F - BLUE




CJSK688TGBU

△ B G - VIOLET




CJSK688TGVL

△ B H - INTERNATIONAL GRAY



CJSK688TGIG

MODEL FILENAME	MO3011AA/01	SIZE A
DRAWING FILENAME	MO3011E1_DC58/01C	
TITLE MINI-COM TX6 PLUS SHIELDED KEYED JACK MODULE CUSTOMER DRAWING		
	PANDUIT TM CORP. TINLEY PARK, ILL 60477	I.I. NUMBER
		PRODUCT SPEC
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010(.3) (.XX) ± .03(.8) ANGLES ±	WORK INSTRUCTION
		SCALE FULL
DRAWN BY MDJr	REVIEW DRAWING NUMBERS	PART NO. CJSK688TG**
DATE 10-22-08		DRAWING NO. 03011-58
CHK'D BMBA		SHEET 2 OF 2

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
2	6-21-10	MDJr	PBD	SEE SHEET ONE FOR CHANGES	03011-58		PBD		
1	1-27-09	MDJr	PBD	SEE SHEET ONE FOR CHANGES	03011-58		VMB		
R	12-01-08	MDJr	BMBA	SEE SHEET ONE FOR CHANGES	03011-58		VMB		