

Product data sheet

Characteristics

70-169-1

Socket, SE Relays general purpose relay accessory, DPDT, 15A, 300 V, 8 pins, screw clamp terminal, 750R/750H series



Main

Product Range	Legacy
Product Type	Socket
Product Compatibility	Relay 750XBXR Relay 750XBXH Relay TDRPRO-5101/5102
Number of Terminals	8
Switch Function	DPDT
Contact Composition	2 NO + 2 NC

Complementary

Rated Current	15 A
[Ue] rated operational voltage	300 V
Contact Terminal Arrangement	Mixed
Connections Terminals	Screw clamp terminals Output screw clamp terminalsstranded
Tightening Torque	0.9 N.m
Fixing Mode	By screw M3.5, M3.5 panel
Shape of Screw Head	Combination roundhead
Product Weight	2.01 oz (57 g)
Width	1.97 in (50 mm)
Depth	2.24 in (57 mm)

Environment

Ambient Air Temperature for Storage	-40...221 °F (-40...105 °C)
Ambient Air Temperature for Operation	-40...131 °F (-40...55 °C)
IP Degree of Protection	IP20
Flame Retardance	UL94-V0
Product Certifications	UL CSA CE

Ordering and shipping details

GTIN	3606480277771
Nbr. of units in pkg.	1
Package weight(Lbs)	2.01 oz (57.0 g)

Packing Units


Unit Type of Package 1	PCE
Package 1 Height	2.24 in (5.7 cm)
Package 1 width	1.97 in (5 cm)
Package 1 Length	0.63 in (1.6 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10

Package 2 Weight	20.11 oz (570.0 g)
Package 2 Height	2.17 in (5.5 cm)
Package 2 width	2.36 in (6 cm)
Package 2 Length	6.50 in (16.5 cm)
Unit Type of Package 3	CAR
Number of Units in Package 3	500
Package 3 Weight	62.83 lb(US) (28.5 kg)
Package 3 Height	12.80 in (32.5 cm)
Package 3 width	13.78 in (35 cm)
Package 3 Length	16.14 in (41 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Approximate Dimensions



Connections and Wiring Diagrams

