



DESCRIPTION: M5 FEMALE - RIGHT ANGLE - 4 POSITION



NOTE:

MATERIAL

HOUSING:

PBT UL94V-0, BLACK

CONTACT:

BRASS

NUT:

BRASS

O-RING:

NBR, BLACK

BACK HOUSING:

PBT UL94V-0, BLACK

DOWN HOUSING:

PBT UL94V-0, BLACK

FINISH

CONTACT:

GOLD PLATED

UNDER PLATE:

NICKEL

NUT:

NICKEL

ELECTRICAL:

RATED CURRENT:

1A

RATED VOLTAGE:

60V

INSULATION RESISTANCE:

100 MOhms MIN.

CONTACT RESISTANCE:

10 mOhms MAX.

WATER PROOF:

IP67


ENVIRONMENT:

OPERATION TEMPERATURE:



-40°C TO +85°C

853-004-213R00Y

1 = GOLD FLASH
4 = 10u" GOLD



NUT



RECOMMENDED PCB LAYOUT

RoHS COMPLIANT

UNITS = INCHES [MM]

DO NOT SCALE FROM DRAWING



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:

M. SIGMON

DATE:

03-04-16

NorComp

SCALE:

NTS

SHEET

1

OF

1

REV

9

DWG NO.

853-004-213R00Y