






THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	C190346	2019/03/05	Vicky	Change Note




Pin Assignments Front View



Pin Assignments Front View

With Liquid Glue




ABD-XXPMMS-SC7001

02:2Pin
08:8Pin

Note:

- * Important Dimension To Check.
- * Waterproof Rate: IP67, Unmated.
- * Housing: Thermoplastic, Black.
- * Pin: Copper Alloy, Gold Plated.
- * Gasket: Rubber, Gray.
- * Nut: Thermoplastic, Black.
- * Use with waterproof cap or dust cap
Maximum Panel Thickness: 3.3mm
- * Use without waterproof cap or dust cap
Maximum Panel Thickness: 4.5mm
- * Gasket and Nut are packed separately
in PE bags. (Gasket/Nut不組裝, 散裝出貨)



UNIT: mm		TITLE STANDARD PANEL SCREW M CONN M PIN			
TOLERANCE		SCALE	SIZE	SHEET	OF
.X ±0.25		2:1	A4	1	1
.XX ±0.1		REV.	WC-REV.	QC: Inspection item	
.XXX ±0.05		B	A.1		
ANGLES ±1°					

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO.	DRAWN BY	DATE
DWG. NO.	Vicky	2019-03-05
ABD-XXPMMS-SC7001	CHECKED BY	DATE
CUSTOMER	Rita	2019-03-05
ALTW	APPROVED BY	DATE
	Max	2019-03-05